



SECURITY GRILLES

SG400

SG400

STEEL

Model SG400 is designed as a transfer grille for medium and maximum security applications. It is constructed with two face plates welded to each end of the sleeve for block wall applications or for pouring in place in concrete walls. The 5/16" round holes allow a greater free area and maximize airflow while minimizing finger penetration and concealment of dangerous objects or contraband.

FEATURES

- Face Plate: 3/16" steel with 5/16" diameter round holes on 7/16" staggered centers and 1" border
- Sleeve: 3/16" steel (available in 6", 8", 10", 12" and 18" lengths)
- Steel construction
- All welded construction
- Standard finish is white (WH)

ACCESSORIES

- Anchor bars (AB) 3/4" diameter x 3" long steel bars positioned 3" from back of face plate on top and bottom of sleeve
- Security bars (SB) 3/4" diameter steel bars on a maximum of 6" centers; security bar grid is tack welded twice at each intersection and welded completely around at the sleeve joint

Available Sizes

Min	Max
6x4	30x30
Product available in 2" increments only.	