

Coil Product Offering



Casing Style	WATER & DX COIL						STEAM COIL					
	3/4" Top and Bottom (T&G Casing)		3/4" Top and Bottom (H Casing)		1 1/2" Top and Bottom (S Casing)		7/8" Top and Bottom (K Casing)		Sloped 1 1/4" to 3/4" x 1 1/4" End Sheet (P Casing)	Sloped 3/4" to 1 1/4" (Q Casing)	Sloped 1 3/4" to 1 1/4" x 1 1/2" End Sheets (R Casing)	1 1/2" Top and Bottom (S Casing)
Product	Solution/Custom		AirPak/CurbPak		AirPak/CurbPak		Solution/Custom		Solution/Custom		AirPak/CurbPak	
Rows	1,2,3,4,5,6,8,10,12		1,2,3,4,5,6,8,10,12		1,2,3,4,5,6,8,10,12		1,2,3,4,5,6,8,10,12		1		1	
Tube Diameter	1/2"	5/8"	1/2"	5/8"	1/2"	5/8"	5/8"		1"		1"	
Tube Material	Copper		Copper		Copper		Copper		Copper		Copper	
Tube Thickness	016, 020, 032	020, 025, 035, 049	016, 020, 032	020, 025, 035, 049	016, 020, 032	020, 025, 035, 049	020, 025, 035, 049		035, 049		035, 049	
Air Flow	Vertical, Horizontal		Vertical, Horizontal		Vertical, Horizontal		Vertical, Horizontal		Horizontal	Vertical	Horizontal	Vertical
Fin Type (wave)	Corrugated	Sine	Corrugated	Sine	Corrugated	Sine	Flat		Corrugated		Corrugated	
Fin Material	Aluminum, Copper		Aluminum, Copper		Aluminum, Copper		Aluminum, Copper		Aluminum, Copper		Aluminum, Copper	
Fin Thickness	Aluminum = 006, 008, 010 Copper = 006, 008		Aluminum = 006, 008, 010 Copper = 006, 008		Aluminum = 006, 008, 010 Copper = 006, 008		Aluminum = 006, 008, 010 Copper = 006, 008		Aluminum = 006, 010 Copper = 006		Aluminum = 006, 010 Copper = 006	
FPI	8,9,10,11,12,13,14		8,9,10,11,12,13,14		8,9,10,11,12,13,14		8,9,10,11,12,13,14		6,8,9,10,11,12,13,14		6,8,9,10,11,12,13,14	
Casing Material	Galvanized, SST		Galvanized, SST		Galvanized, SST		Galvanized, SST		Galvanized, SST		Galvanized, SST	
Header Material	Copper, Red Brass		Copper, Red Brass		Copper, Red Brass		Copper, Red Brass		Copper		Copper	
Connection Material	Steel, Red Brass, Copper		Steel, Red Brass, Copper		Steel, Red Brass, Copper		Steel, Red Brass, Copper		Red Brass, Copper		Red Brass, Copper	
Connection Type	MPT, FPT, Grooved, Sweat		MPT, Grooved, Sweat		MPT, Grooved, Sweat		MPT, Grooved, Sweat		MPT		MPT	
Maximum Fin Height (implied: #SC=1)	60.00"	60.25"	Standard: 47.5" Tall: 95"	Standard: 48.25" Tall: 96.5"	Standard: 47.5" Tall: 95"	Standard: 48.25" Tall: 96.5"	5/8" = 48"		60"	48"	Standard: 60" Tall: 96"	Standard: 48" Tall: 96"
Maximum Fin Length	6 THRU 168		6 THRU 168		6 THRU 168		6 THRU 168		6 THRU 144		6 THRU 144	

20 day standard shipment

Quick Ship - 5 day and 10 day shipment offerings are available

Coil Coatings

- **Heresite/Phenolic** – Ideal for coils exposed to high corrosive fumes and salt atmosphere
- **Electrofin** - Protects coils against a broad range of chemicals while limiting the affect of the coil performance

Replacement Coils

- We offer replacement coils for all JCI air handling units and most other manufacturer's air handlers.
- Please contact your account manager for ordering.