



DIMENSIONS - In [mm]

UNIT SIZE	A	B	C	D
03 & 04	18 [457]	23-3/8 [594]	16 [406]	8 [203]
06 & 08	20 [508]	25-3/8 [645]	18 [457]	12 [305]
10 & 12	24 [610]	29-3/8 [746]	22 [559]	14 [356]

NOTES:

- All dimensions are Inches [mm]. Metric values are soft conversion.
- All dimensions are $\pm 1/4$ [6mm].
- Thermostat is shipped loose and may be unit surface mounted or remote wall mounted.
- Wiring from electrical entry point to control enclosure is furnished and installed by others in field.
- Risers available from 3/4" [19mm] to 3" [76mm] diameter with 1/2" [13mm] thick insulation, and 3/4" [19mm] to 2-1/2" [64mm] diameter with 3/4" [19mm] thick insulation.
- Riser length is 120" [3048mm] max, 100" [2540mm] min.
- All units are back riser, front single supply, Arg. BFOO only.
- Factory mounted risers shown. See drawing VH-105 for shipped loose riser details.
- Standard cabinet finish is "Pearl White Satin".
- Floor and ceiling trim furnished and installed by others.

TITLE:

MODEL VHE VERTICAL EXPOSED HIGH RISE FAN COIL UNIT



DRN BY: HANK	DATE: 08/27/04	SCALE: 1=31.5	DRAWING NO.
CKD BY: HANK	DATE: 8/27/04	REV: 00	

74-80004

THIS DRAWING CONTAINS PROPRIETARY DATA. UNAUTHORIZED DISCLOSURE, REPRODUCTION, OR USE IS STRICTLY PROHIBITED WITHOUT WRITTEN PERMISSION

DO NOT SCALE DRAWING. DIMENSIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE. CONTACT FACTORY FOR CERTIFIED DRAWINGS.