



NOTES:

1. All dimensions are inches [millimeters].
All dimensions are $\pm 1/4"$ [6mm]. Metric values are soft conversion.
2. All drawings subject to change without prior notice.
3. Right hand unit shown, left hand unit opposite.
4. See coil connection drawing 50-80020 and 50-80021 for coil connection sizes and locations.
5. Dimensions shown apply to filter access panel for unit sizes 04-08 only.



TOP VIEW

DRAIN OUTLET,
SEE NOTE 4



FRONT VIEW

COIL CONNECTIONS,
SEE NOTE 4

7/8 X 1-1/8
DOUBLE KO
TYP BOTH SIDES

36" SERVICE CLEARANCE
AS REQUIRED BY NEC

COIL & DRAIN PAN
ACCESS PANEL

2-1/2 [64]


1 [25]

SIDE VIEW

2-1/2 [64]

1 [25]

SIDE VIEW



SIDE VIEW

SIZES 04-08 ONLY
SEE NOTE 5

DIMENSIONS - In[mm]

UNIT SIZE	A	B	C	D	E	F	G	H	J
04-06	22 [559]	15 [381]	48 [1219]	7-1/2 [190]	17 [432]	5-3/4 [146]	1-1/4 [32]	13 [330]	20 [508]
08	22 [559]	15 [381]	48 [1219]	10 [254]	17 [432]	3-1/4 [83]	1-1/4 [32]	13 [330]	20 [508]
10-12	29 [737]	18 [457]	48 [1219]	12-3/4 [324]	24 [610]	3-3/4 [95]	1-1/4 [32]	16 [406]	27 [688]
16-20	46 [1168]	18 [457]	48 [1219]	12-3/4 [324]	39 [991]	3-3/4 [95]	3 [76]	16 [406]	44 [1118]

TITLE:

MODEL CDV
VERTICAL DIRECT DRIVE AIR HANDLING UNIT
STD BOTTOM RETURN



ENVIRO-TEC®

DRN BY:
JGH

DATE:
7/23/19

SCALE:
NTS

DRAWING NO.

CKD BY:
DPB

DATE:
7/23/19

REV:
A

50-80019

THIS DRAWING CONTAINS PROPRIETARY DATA.
UNAUTHORIZED DISCLOSURE, REPRODUCTION, OR USE
IS STRICTLY PROHIBITED WITHOUT WRITTEN PERMISSION

DO NOT SCALE DRAWING
DIMENSIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE.
CONTACT FACTORY FOR CERTIFIED DRAWINGS.