


**STANDARD FEATURES:**

1. 22 GAUGE GALVANIZED STEEL CASING CONSTRUCTION
2. 1/2" DUAL DENSITY LINING
3. ROUND INLET COMPATIBLE WITH NOMINAL RIGID AND FLEX DUCT CONNECTIONS
4. SLIP AND DRIVE DISCHARGE CONNECTION
5. PATENTED FLO-CROSS MULTIPOINT FLO SENSOR
6. DAMPER SHAFT WITH DELRIN BEARINGS AND POSITION INDICATOR
7. LOW LEAKAGE DAMPER WITH SEAL
8. INTEGRAL ATTENUATOR
9. RIGHT OR LEFT HAND CONFIGURATIONS AVAILABLE (RIGHT HAND SHOWN)



**LINER OPTIONS:**

- 1/2" DUAL DENSITY
- 1" DUAL DENSITY
- ENVIROSEAL
- INSULGUARD
- NO LINER
- GAL. SHEET METAL LINER

SEE SUBMITTAL SD-7005 FOR LINER PROPERTIES

**CONSTRUCTION:**

- 20 GAUGE
- ACCESS DOOR
- CAM LATCHES

CAM LATCHES REQUIRE AN ACCESS DOOR

**ACCESSORIES:**

- CONTROL ENCLOSURE
- DISC. SWITCH
- DUSTTIGHT SEAL
- HANGER BKT

**TRANSFORMER**

- 120V / 24V
- 208V / 24V
- 240V / 24V
- 277V / 24V
- 480V / 24V

SIZE	CFM RANGE 0 or MIN - MAX
24	0 or 1420 - 7100

JOB NAME: \_\_\_\_\_  
 LOCATION: \_\_\_\_\_  
 ARCHITECT: \_\_\_\_\_  
 ENGINEER: \_\_\_\_\_  
 CONTRACTOR: \_\_\_\_\_

SUBMITTED BY: \_\_\_\_\_  
 DATE: AUGUST '02  
 DRAWING NUMBER: SD-7011

**SDV - SINGLE DUCT TERMINAL UNIT**

HIGH CAPACITY BASE UNIT WITH INTEGRAL ATTENUATOR