



**SG200**

# SECURITY GRILLES

## SG200

### STEEL

The SG200 security grille is designed for medium and maximum security applications. The 5/16" round holes allow a greater free area and maximize airflow while minimizing finger penetration and concealment of dangerous objects or contraband. The SG200 can be used for either supply or return applications.

### FEATURES

- Face Plate: 3/16" steel with 5/16" diameter round holes on 9/32" staggered centers and 1" border
- Sleeve: 3/16" steel (available in 6", 8", 10", 12" and 18" lengths)
- Steel construction
- All welded construction
- Standard finish is white (WH)

### ACCESSORIES

- Angle frame (AF) 1-1/2" x 1-1/2" x 3/16" steel angle iron welded at corners (shipped loose and unpainted for field mounting)
- Anchor bars (AB) 3/4" diameter x 3" long steel bars positioned 3" from back of face plate on top & bottom of sleeve
- Security bars (SB) 3/4" diameter steel bars on a maximum of 6" centers; security bar grid is tack welded twice at each intersection and welded completely around at the sleeve joint
- Steel opposed blade (SDFO - face operated) or (SDRO - rear operated) damper is welded into sleeve

### Available Sizes

Min	Max
6x4	30x30

Product available in 2" increments only. 9x9 is the only odd size available.