


STANDARD FEATURES:

1. 22 GAUGE GALVANIZED STEEL CASING CONSTRUCTION
2. 1/2" DUAL DENSITY LINING
3. ROUND INLET COMPATIBLE WITH NOMINAL RIGID AND FLEX DUCT CONNECTIONS
4. SLIP AND DRIVE DISCHARGE CONNECTION
5. PATENTED FLO-CROSS MULTIPOINT FLO SENSOR
6. DAMPER SHAFT WITH DELRIN BEARINGS AND POSITION INDICATOR
7. LOW LEAKAGE DAMPER WITH SEAL
8. RIGHT OR LEFT HAND CONFIGURATIONS AVAILABLE (RIGHT HAND SHOWN)



SIZE	CFM RANGE	LINER OPTIONS: <input type="checkbox"/> 1/2" DUAL DENSITY <input type="checkbox"/> 1" DUAL DENSITY <input type="checkbox"/> ENVIROSEAL <input type="checkbox"/> INSULGUARD <input type="checkbox"/> NO LINER <input type="checkbox"/> GAL. SHEET METAL LINER <small>SEE SUBMITTAL SD-7005 FOR LINER PROPERTIES</small>	CONSTRUCTION: <input type="checkbox"/> 20 GAUGE <input type="checkbox"/> ACCESS DOOR <input type="checkbox"/> CAM LATCHES CAM LATCHES REQUIRE AN ACCESS DOOR	ACCESSORIES: <input type="checkbox"/> CONTROL ENCLOSURE <input type="checkbox"/> DISC. SWITCH <input type="checkbox"/> DUSTTIGHT SEAL <input type="checkbox"/> HANGER BKT TRANSFORMER <input type="checkbox"/> 120V / 24V <input type="checkbox"/> 208V / 24V <input type="checkbox"/> 240V / 24V <input type="checkbox"/> 277V / 24V <input type="checkbox"/> 480V / 24V
	0 or MIN - MAX			
24	0 or 1420 - 7100			

JOB NAME: _____ LOCATION: _____ ARCHITECT: _____ ENGINEER: _____ CONTRACTOR: _____	SUBMITTED BY: _____ <hr/> DATE: AUGUST '02 <hr/> DRAWING NUMBER: SD-7009	SDV - SINGLE DUCT TERMINAL UNIT HIGH CAPACITY BASE UNIT
--	--	---