


Product Dimensions

FPP Basic Model





* Note: Digital or Analog control enclosure is $20" \times 11\frac{7}{8}"$,
Pneumatic enclosure is $17" \times 15"$

UNIT SIZE	INLET SIZE	HP	A	B	C		E	F	G	H	INDUCED		DISCHARGE		M
											I	J	K	L	
2	06	1/10	29	15	4 7/8	15	15	5 7/8	7 1/2	6 7/8	13	13	11 1/2	11 1/2	1 3/4
2	08	1/10	29	15	4 7/8	15	15	7 7/8	7 1/2	6 7/8	13	13	11 1/2	11 1/2	1 3/4
3	08	1/10	29	15	4 7/8	15	15	7 7/8	7 1/2	6 7/8	13	13	11 1/2	11 1/2	1 3/4
3	10	1/10	29	15	4 7/8	15	15	9 7/8	7 1/2	6 7/8	13	13	11 1/2	11 1/2	1 3/4
4	10	1/4	29	15	4 7/8	15	15	9 7/8	7 1/2	6 7/8	13	13	11 1/2	11 1/2	1 3/4
4	12	1/4	29	15	6 7/8	15	15	11 7/8	7 1/2	6 7/8	13	13	11 1/2	11 1/2	1 3/4
5	12	1/2	37	19	6 7/8	19	17 3/4	11 7/8	8 7/8	9	17	15 3/4	14	15 1/2	1 7/8
5	14	1/2	37	19	6 7/8	19	17 3/4	13 7/8	8 7/8	9	17	15 3/4	14	15 1/2	1 7/8
6	14	1/2	37	19	6 7/8	19	17 3/4	13 7/8	8 7/8	9	17	15 3/4	14	15 1/2	1 7/8
6	16	1/2	37	19	6 7/8	19	17 3/4	15 7/8	8 7/8	9	17	15 3/4	14	15 1/2	1 7/8
7	16	3/4	37	19	6 7/8	19	17 3/4	15 7/8	8 7/8	9	17	15 3/4	14	15 1/2	1 7/8

Product Dimensions

FPP Hot Water Heat






* Note: Digital or Analog control enclosure is 31" x 11 7/8",
Pneumatic control enclosure 17" x 15".

UNIT SIZE	INLET SIZE	HP	A	B	C		E	F	G	H	INDUCED		DISCHAR		M
											I	J	K	L	
2	06	1/10	29	15	4 7/8	15	15	5 7/8	7 1/2	6 7/8	13	13	12 1/2	15	1 3/4
2	08	1/10	29	15	4 7/8	15	15	7 7/8	7 1/2	6 7/8	13	13	12 1/2	15	1 3/4
3	08	1/10	29	15	4 7/8	15	15	7 7/8	7 1/2	6 7/8	13	13	12 1/2	15	1 3/4
3	10	1/10	29	15	4 7/8	15	15	9 7/8	7 1/2	6 7/8	13	13	12 1/2	15	1 3/4
4	10	1/4	29	15	4 7/8	15	15	9 7/8	7 1/2	6 7/8	13	13	12 1/2	22	1 3/4
4	12	1/4	29	15	6 7/8	15	15	11 7/8	7 1/2	6 7/8	13	13	12 1/2	22	1 3/4
5	12	1/2	37	17 3/4	6 7/8	19	17 3/4	11 7/8	8 7/8	9	17	15 3/4	15	22	1 7/8
5	14	1/2	37	17 3/4	6 7/8	19	17 3/4	13 7/8	8 7/8	9	17	15 3/4	15	22	1 7/8
6	14	1/2	37	17 3/4	6 7/8	19	17 3/4	13 7/8	8 7/8	9	17	15 3/4	15	24 1/2	1 7/8
6	16	1/2	37	17 3/4	6 7/8	19	17 3/4	15 7/8	8 7/8	9	17	15 3/4	15	24 1/2	1 7/8
7	16	3/4	37	17 3/4	6 7/8	19	17 3/4	15 7/8	8 7/8	9	17	15 3/4	15	24 1/2	1 7/8

Product Dimensions

FPP Electric Reheat



* Note: Digital or Analog control enclosure is 31" x 11 7/8",
Pneumatic control enclosure is 17" x 15".

UNIT SIZE	INLET SIZE	HP	A	B	C		E	F	G	H	INDUCED		DISCHARGE		M
											I	J	K	L	
2	06	1/10	29	15	4 7/8	15	15	5 7/8	7 1/2	6 7/8	13	13	11 1/2	11 1/2	1 3/4
2	08	1/10	29	15	4 7/8	15	15	7 7/8	7 1/2	6 7/8	13	13	11 1/2	11 1/2	1 3/4
3	08	1/10	29	15	4 7/8	15	15	7 7/8	7 1/2	6 7/8	13	13	11 1/2	11 1/2	1 3/4
3	10	1/10	29	15	4 7/8	15	15	9 7/8	7 1/2	6 7/8	13	13	11 1/2	11 1/2	1 3/4
4	10	1/4	29	15	4 7/8	15	15	9 7/8	7 1/2	6 7/8	13	13	11 1/2	11 1/2	1 3/4
4	12	1/4	29	15	6 7/8	15	15	11 7/8	7 1/2	6 7/8	13	13	11 1/2	11 1/2	1 3/4
5	12	1/2	37	17 3/4	6 7/8	19	17 3/4	11 7/8	8 7/8	9	17	15 3/4	14	15 1/2	1 7/8
5	14	1/2	37	17 3/4	6 7/8	19	17 3/4	13 7/8	8 7/8	9	17	15 3/4	14	15 1/2	1 7/8
6	14	1/2	37	17 3/4	6 7/8	19	17 3/4	13 7/8	8 7/8	9	17	15 3/4	14	15 1/2	1 7/8
6	16	1/2	37	17 3/4	6 7/8	19	17 3/4	15 7/8	8 7/8	9	17	15 3/4	14	15 1/2	1 7/8
7	16	3/4	37	17 3/4	6 7/8	19	17 3/4	15 7/8	8 7/8	9	17	15 3/4	14	15 1/2	1 7/8