


STANDARD FEATURES:

1. 22 GAUGE GALVANIZED STEEL CASING CONSTRUCTION
2. 1/2" DUAL DENSITY LINING
3. ROUND INLET COMPATIBLE WITH NOMINAL RIGID AND FLEX DUCT CONNECTIONS
4. SLIP AND DRIVE DISCHARGE CONNECTION
5. PATENTED FLO-CROSS MULTIPOINT FLO SENSOR
6. DAMPER SHAFT WITH DELRIN BEARINGS AND POSITION INDICATOR
7. LOW LEAKAGE DAMPER WITH SEAL
8. RIGHT OR LEFT HAND CONFIGURATIONS AVAILABLE (RIGHT HAND SHOWN)



UNIT SIZE	CFM RANGE MIN TO MAX	L	H	W	A	D	F	G	LINER OPTIONS:	CONSTRUCTION:	ACCESSORIES:
4	0/45 - 230	15 1/2	8	12	5 3/8	3 7/8	2 1/8	7 1/4	<input type="checkbox"/> 1/2" DUAL DENSITY	<input type="checkbox"/> 20 GAUGE	<input type="checkbox"/> CONTROL ENCLOSURE
5	0/70 - 360	15 1/2	8	12	5 3/8	4 7/8	2 1/8	7 1/4	<input type="checkbox"/> 1" DUAL DENSITY	<input type="checkbox"/> ACCESS DOOR	<input type="checkbox"/> DISC. SWITCH
6	0/100 - 520	15 1/2	8	12	3 3/8	5 7/8	2 1/8	7 1/4	<input type="checkbox"/> ENVIROSEAL	<input type="checkbox"/> CAM LATCHES	<input type="checkbox"/> DUSTTIGHT SEAL
7	0/140 - 710	15 1/2	10	12	3 3/8	6 7/8	1 1/8	7 1/4	<input type="checkbox"/> INSULGUARD	CAM LATCHES REQUIRE AN ACCESS DOOR	<input type="checkbox"/> HANGER BKT
8	0/185 - 925	15 1/2	10	12	3 3/8	7 7/8	1 1/8	7 1/4	<input type="checkbox"/> NO LINER		<input type="checkbox"/> TRANSFORMER
10	0/290 - 1450	15 1/2	12 1/2	14	3 3/8	9 7/8	-	5 1/4	<input type="checkbox"/> GAL. SHEET METAL LINER		<input type="checkbox"/> 120V / 24V
12	0/420 - 2100	15 1/2	15	16	3 3/8	11 7/8	-	5 1/4	SEE SUBMITTAL SD-7005 FOR LINER PROPERTIES		<input type="checkbox"/> 208V / 24V
14	0/580 - 2900	15 1/2	17 1/2	20	3 3/8	13 7/8	-	3 1/4			<input type="checkbox"/> 240V / 24V
16	0/740 - 3700	15 1/2	18	24	3 3/8	15 7/8	-	3 1/4			<input type="checkbox"/> 277V / 24V
											<input type="checkbox"/> 480V / 24V

JOB NAME: _____
 LOCATION: _____
 ARCHITECT: _____
 ENGINEER: _____
 CONTRACTOR: _____

SUBMITTED BY: _____
 DATE: JANUARY 2020
 DRAWING NUMBER: SD-7006

SDV - SINGLE DUCT TERMINAL UNIT

 BASE UNIT