



T115

# GRILLES & REGISTERS

## Heavy Duty Return Tri-Flex Heavy Duty

### STEEL

T115 heavy duty return grilles and registers are designed to take maximum abuse in areas requiring heavy duty applications such as gymnasiums, arenas, and industrial areas. The construction consists of a 16 gauge margin with 14 gauge bars. Stationary deflection bars are spaced on 1/2" centers and factory set at 38° or bars are spaced on 3/8" centers and factory set at 0° deflection. The appearance matches the T125 and T155 series of heavy duty supply grilles and registers.

### FEATURES

- 1-1/4" nominal overlap margin
- Heavy duty steel construction (16 gauge margin, 14 gauge bars)
- Stationary bars spaced on 1/2" centers with 38° deflection
- Stationary bars spaced on 3/8" centers with 0° deflection
- Choice of horizontal face bars (H), or vertical face bars (V)
- Support bars on 6" centers
- Standard finish is White (WH)

### ACCESSORIES

- Optional steel opposed blade damper (SOBD) is factory mounted and screwdriver operated from the face of grille
- Optional steel mounting frame (45) available for use in plaster applications to facilitate grille removal

Available Sizes in One Piece	
Minimum	Maximum
6x4	48x48
Product available in one inch increments of width and height. Sizes greater than 48x48 are supplied in multiple sections.	