



PRODUCT DIMENSIONS

SDV Basic Unit

SIZES 4-16




PLAN VIEW




INLET VIEW

SIZES 24



PLAN VIEW



INLET VIEW


Unit Size	CFM Range	Length (L)	Height (H)	Width (W)	Inlet Diameter (D)
	Min To Max				
4	0/45-230	15-1/2	8	12	3-7/8
5	0/70-360	15-1/2	8	12	4-7/8
6	0/100-520	15-1/2	8	12	5-7/8
7	0/140-710	15-1/2	10	12	6-7/8
8	0/185-925	15-1/2	10	12	7-7/8
10	0/290-1450	15-1/2	12-1/2	14	9-7/8
12	0/420-2100	15-1/2	15	16	11-7/8
14	0/580-2900	15-1/2	17-1/2	20	13-7/8
16	0/740-3700	15-1/2	18	24	15-7/8
24	0/1420-7100	15	see above	see above	see above

*5-3/8" for sizes 4 and 5 (A reducer is used on a size 6 inlet)



PRODUCT DIMENSIONS

SDV w/Integral Discharge Attenuator


SIZES 4-16



SIZES 24



INLET VIEW



INLET VIEW

Unit Size	CFM Range	Length (L)	Height (H)	Width (W)	Inlet Diameter (D)
	Min To Max				
4	0/45-230	39-1/2	8	12	3-7/8
5	0/70-360	39-1/2	8	12	4-7/8
6	0/100-520	39-1/2	8	12	5-7/8
7	0/140-710	39-1/2	10	12	6-7/8
8	0/185-925	39-1/2	10	12	7-7/8
10	0/290-1450	39-1/2	12-1/2	14	9-7/8
12	0/420-2100	39-1/2	15	16	11-7/8
14	0/580-2900	39-1/2	17-1/2	20	13-7/8
16	0/740-3700	39-1/2	18	24	15-7/8
24	0/1420-7100	39-1/2	see above	see above	see above


*5-3/8" for sizes 4 and 5 (A reducer is used on a size 6 inlet)

DIMENSIONS IN INCHES


PRODUCT DIMENSIONS

SDV w/Hot Water Reheat

SIZES 4-16




PLAN VIEW




INLET VIEW

SIZES 24



PLAN VIEW



INLET VIEW

Unit Size	CFM Range	Length* (L)	Height (H)	Width (W)	Inlet Diameter (D)
	Min To Max				
4	0/45-230	20-1/2	8	12	3-7/8
5	0/70-360	20-1/2	8	12	4-7/8
6	0/100-520	20-1/2	8	12	5-7/8
7	0/140-710	20-1/2	10	12	6-7/8
8	0/185-925	20-1/2	10	12	7-7/8
10	0/290-1450	20-1/2	12-1/2	14	9-7/8
12	0/420-2100	20-1/2	15	16	11-7/8
14	0/580-2900	23	17-1/2	20	13-7/8
16	0/740-3700	23	18	24	15-7/8
24	0/1420-7100	20	see above	see above	see above


*Add 2-1/4" to "L" for 3 & 4 row hot water coils

**5-3/8" for sizes 4 and 5 (A reducer is used on a size 6 inlet)




PRODUCT DIMENSIONS

SDV w/ Hot Water Heat & Integral Discharge Attenuator

SIZES 4-16



SIZES 24



Unit Size	CFM Range	Length* (L)	Height (H)	Width (W)	Inlet Diameter (D)
	Min To Max				
4	0/45-230	44-1/2	8	12	3-7/8
5	0/70-360	44-1/2	8	12	4-7/8
6	0/100-520	44-1/2	8	12	5-7/8
7	0/140-710	44-1/2	10	12	6-7/8
8	0/185-925	44-1/2	10	12	7-7/8
10	0/290-1450	44-1/2	12-1/2	14	9-7/8
12	0/420-2100	44-1/2	15	16	11-7/8
14	0/580-2900	47	17-1/2	20	13-7/8
16	0/740-3700	47	18	24	15-7/8
24	0/1420-7100	44-1/2	see above	see above	see above

*Add 2-1/4" to "L" for 3 & 4 row hot water coil


**5-3/8" for sizes 4 and 5 (A reducer is used on a size 6 inlet)

DIMENSIONS IN INCHES


PRODUCT DIMENSIONS

SDV w/ Electric Heat & Integral Discharge Attenuator

SIZES 4-16




PLAN VIEW




INLET VIEW

SIZES 24



PLAN VIEW



INLET VIEW



Unit Size	CFM Range	Length (L)	Height (H)	Width (W)	Inlet Diameter (D)
	Min To Max				
4	0/45-230	39-1/2	8	12	3-7/8
5	0/70-360	39-1/2	8	12	4-7/8
6	0/100-520	39-1/2	8	12	5-7/8
7	0/140-710	39-1/2	10	12	6-7/8
8	0/185-925	39-1/2	10	12	7-7/8
10	0/290-1450	39-1/2	12-1/2	14	9-7/8
12	0/420-2100	39-1/2	15	16	11-7/8
14	0/580-2900	39-1/2	17-1/2	20	13-7/8
16	0/740-3700	39-1/2	18	24	15-7/8
24	0/1420-7100	39-1/2	see above	see above	see above

Electric heat unit is standard with integral sound attenuator
 **5-3/8" for sizes 4 and 5 (A reducer is used on a size 6 inlet)