

CB778

Atomizing Super-Fine Mist Humidifier Horticulture, Humidors & Other Applications

Horticulture Applications

- Greenhouses
- Growrooms
- Grow Tents
- Mushrooms

Features

- Reliable product uses commercial-grade motor
- Operates free-standing or via duct connection
- Standard 120 volt wall plug electrical connection
- Rubber non-slipping feet
- 1/4" copper or plastic compression water inlet
- Water inlet adaptable to 1/4" push fit connection
- Internal float automatically controls water inlet
- Safety overflow hose can be connected to a drain
- If a humidistat is required, TRION recommends using a IHC-200 Plug & Play Humidity Controller



Performance

- Quiet, reliable, low maintenance
- Total power consumption less than 100 watts
- Capacity output = 6 gallons per day at 120° F

Warranty

- 1 year limited warranty

Optional Accessories

- For wall mount bracket use TRION P/N 186C
- If thru-wall mounting, use TRION P/N 269532-301

