



SECURITY GRILLES

SG700



SG700

ALUMINUM

The SG700 aluminum security bar grille is designed for minimum security applications. With heavy duty aluminum construction, it is ideal for high humidity areas such as bathrooms and showers where security is still needed. The SG700 can be used for supply or return applications.

FEATURES

- Bar grille: 3/16" x 3/4" welded aluminum bars with 1/8" aluminum frame; bars are spaced on 1/2" centers with 0° deflection
- Sleeve: 1/8" aluminum (available in 6", 8", 10", 12" and 18" lengths)
- Aluminum construction
- All welded construction
- Standard finish is white (WH)

ACCESSORIES

- Angle frame (AF) 1-1/2" x 1-1/2" x 1/8" aluminum angle iron welded at corners (shipped loose and unpainted for field mounting)
- Anchor bars (AB) 1/2" diameter x 3" long aluminum bars positioned 3" from back of face plate on top and bottom of sleeve
- Security bars (SB) 1/2" diameter aluminum bars on a maximum of 6" centers; security bar grid is tack welded twice at each intersection and welded completely around at the sleeve joint
- Aluminum opposed blade damper (ADFO - face operated) or (ADRO - rear operated) is welded into sleeve

Available Sizes

Min	Max
6x4	30x30
Product available in 2" increments only.	