



PP

PERFORATED DIFFUSERS

Face Mounted Pattern Deflectors PP, APP Series

STEEL

STEEL
BACKPAN
ALUMINUM
FACE

The PP series model perforated ceiling diffusers are recommended for heating, ventilating and cooling in constant and variable volume systems. The removable hinged perforated faces blend with any ceiling. Pattern deflectors are adjustable for 4, 3, 2 or 1-way horizontal air diffusion patterns to fit a multitude of room requirements. Four standard margin styles along with a square or round neck are available to maximize versatility.

FEATURES

- Removable hinged face, available in a flush or drop style, provides easy access for cleaning, maintenance, and pattern adjustment without disturbing the ceiling
- Four adjustable face mounted stamped deflectors provide 4, 3, 2 or 1-way horizontal discharge patterns
- Available in square or round neck, no transitions needed
- Steel construction is standard. Steel backpan with aluminum face is optional
- Perforated face has 3/16" holes on 1/4" staggered centers and no less than 51% free area
- Standard finish is white (WH)
- Optional black backpan with white face and margin finish (BW) available
- Matching returns available. Refer to model PR
- Square or round dampers must be ordered separately and field installed

ACCESSORIES

- Round butterfly damper (RBN,RBD)
- Round opposed blade damper (RON,ROD)
- Round radial blade damper (RRN,RRD)

Note: Dampers are ordered separately and shipped loose for field installation.

PP, APP Available Sizes						
Neck Size (in.)	Module Sizes					
	12x12	16x16	20x20	24x12	24x24	48x24
6	X	X	X	X	X,Y	X
8		X	X		X,Y	X
10		X	X		X,Y	X
12			X		X,Y	X
14			X		X,Y	X
16					X,Y	X
6x6	X	X	X	X	X,Y	X
8x8		X	X		X,Y	X
10x10		X	X		X,Y	X
12x12			X		X,Y	X
14x14					X,Y	X
16x16					X,Y	X

"X" denotes availability for model PP Margin styles: SF, LT, PL and TG

"Y" denotes availability for model APP Margin styles: SF, LT and PL

Perforated
Diffusers