



SECURITY GRILLES

SG600



SG600

STEEL

The SG600 steel security bar grille is designed for medium security applications. Heavy duty blades pierce the frame and are individually welded to provide necessary security without the confining appearance of a standard prison grille. The stationary blades are spaced on 3/8" centers with 38° deflection and are backed by a heavy woven steel screen held in place by welded angles.

FEATURES

- Bar grille: 14 gauge steel blades reinforced by 14 gauge mullions on 3" centers; bars are spaced on 3/8" centers with 38° deflection
- Mesh screen: 10 gauge x #2 mesh wire retained by a 14 gauge channel
- Sleeve: 14 gauge steel, wrap around corner construction with stitch welded seams (available in 6", 8", 10", 12" & 18" lengths)
- Steel construction
- All welded construction
- Standard finish is white (WH)

ACCESSORIES

- Angle frame (AF) 1-1/2" x 1-1/2" x 3/16" steel angle iron welded at corners (shipped loose and unpainted for field mounting)
- Anchor bars (AB) 3/4" diameter x 3" long steel bars positioned 3" from back of face plate on top and bottom of sleeve
- Security bars (SB) 3/4" diameter steel bars on a maximum of 6" centers; security bar grid is tack welded twice at each intersection and welded completely around at the sleeve joint
- Steel opposed blade damper (SDFO - face operated) or (SDRO - rear operated) is welded into sleeve

Available Sizes

Min	Max
6x4	30x30
Product available in 2" increments only.	