


STANDARD FEATURES:

1. 22 GAUGE GALVANIZED STEEL CASING CONSTRUCTION
2. 1/2" DUAL DENSITY LINING
3. ROUND INLET COMPATIBLE WITH NOMINAL RIGID AND FLEX DUCT CONNECTIONS
4. SLIP AND DRIVE DISCHARGE CONNECTION
5. PATENTED FLO-CROSS MULTIPOINT FLO SENSOR
6. DAMPER SHAFT WITH DELRIN BEARINGS AND POSITION INDICATOR
7. LOW LEAKAGE DAMPER WITH SEAL
8. HOT WATER HEAT (SD-7007)
9. RIGHT OR LEFT HAND CONFIGURATIONS AVAILABLE (RIGHT HAND SHOWN)



*DIM LISTED FOR 1 & 2 ROW COILS,
ADD 2-1/4" FOR 3 OR 4 ROW COILS

SIZE	CFM RANGE 0 or MIN - MAX
24	0 or 1420 - 7100

LINER OPTIONS:

- 1/2" DUAL DENSITY
- 1" DUAL DENSITY
- ENVIROSEAL
- INSULGUARD
- NO LINER
- GAL. SHEET METAL LINER

SEE SUBMITTAL SD-7005
FOR LINER PROPERTIES

CONSTRUCTION:

- 20 GAUGE
- ACCESS DOOR
- CAM LATCHES

CAM LATCHES REQUIRE AN ACCESS DOOR

ACCESSORIES:

- CONTROL ENCLOSURE
- DISC. SWITCH
- DUSTTIGHT SEAL
- HANGER BKT

TRANSFORMER

- 120V / 24V
- 208V / 24V
- 240V / 24V
- 277V / 24V
- 480V / 24V

JOB NAME: _____
 LOCATION: _____
 ARCHITECT: _____
 ENGINEER: _____
 CONTRACTOR: _____

SUBMITTED BY: _____

DATE: FEBRUARY '03

DRAWING NUMBER: SD-7013

SDV - SINGLE DUCT TERMINAL UNIT

HIGH CAPACITY WITH HOT WATER COILS