



PRODUCT DIMENSIONS

BPS Basic Unit

Plan View



Side View




Size	CFM (Max)	A	B		C	D	H	L	W
			w/o Man. Damper	w/ Man. Damper					
6	500	7 1/8	2	4 1/4	5 9/16	5 7/8	11 1/8	12 3/8	12 7/8
8	900	7 1/8	2	5 1/4	5 9/16	7 7/8	11 1/8	12 3/8	12 7/8
10	1300	8 1/8	2	6 1/4	6 9/16	9 7/8	13 1/8	14 3/8	14 7/8
12	2000	10 1/8	2	7 1/4	8 9/16	11 7/8	17 1/8	18 3/8	18 7/8
14	2500	10 1/8	2	8 1/4	8 9/16	13 7/8	17 1/8	18 3/8	18 7/8
16	3600	12 1/8	2	9 1/4	10 9/16	15 7/8	21 1/8	22 3/8	22 7/8
18	4400	12 1/8	2	10 1/4	10 9/16	17 7/8	21 1/8	22 3/8	22 7/8



PRODUCT DIMENSIONS

BPS with Multiple Outlets



Size	CFM (Max)	A		B	C	D	E	F	L	H	W
		w/o Man. Damper	w/ Man. Damper								
6	500	2	4 1/4	5 7/8	5 1/4	5 7/8	5 1/8	10	38 3/8	11 1/8	12 7/8
8	900	2	5 1/4	7 7/8	5 1/4	5 7/8	5 1/8	10	38 3/8	11 1/8	12 7/8
10	1300	2	6 1/4	9 7/8	6 1/4	7 7/8	6 1/8	12	44 3/8	13 1/8	14 7/8
12	2000	2	7 1/4	11 7/8	8 1/4	7 7/8	6 1/2	12	52 3/8	17 1/8	18 7/8
14	2500	2	8 1/4	13 7/8	8 1/4	9 7/8	6 1/8	12	52 3/8	17 1/8	18 7/8
16	3600	2	9 1/4	15 7/8	10 1/4	9 7/8	7 1/8	14	56 3/8	21 1/8	22 7/8
18	4400	2	10 1/4	17 7/8	10 1/4	9 7/8	7 1/8	14	56 3/8	21 1/8	22 7/8



DIMENSIONS IN INCHES