

1 ROW STEAM COIL

DIMENSIONS - In [mm]

See Dwgs.
CCC-002, Figs. 4 & 6
CCC-004, Fig. 11

HEATING ONLY AND PRE-HEAT						
UNIT SIZE	STM CONN	COND CONN	E	F	G	H
08						
12	1-1/8 [29]	7/8 [22]	6-1/8 [156]	4-3/8 [112]	10-7/8 [277]	3-1/2 [89]
16						
20	1-3/8 [35]	1-1/8 [29]	6-1/4 [159]	4-1/4 [115]	12-1/8 [308]	3-5/8 [92]
30	1-5/8 [42]		6-3/8 [163]	4-1/8 [105]	13-3/8 [340]	
40	2-1/8 [54]	1-3/8 [35]	6-1/2 [166]	4 [102]	14-5/8 [372]	3-3/4 [96]

RE-HEAT W/3 ROW CLG							RE-HEAT W/4 ROW CLG						
UNIT SIZE	STM CONN	COND CONN	E	F	G	H	UNIT SIZE	STM CONN	COND CONN	E	F	G	H
08							08						
12	1-1/8 [29]	7/8 [22]	11-3/8 [289]	9-5/8 [244]	10-7/8 [277]	3-1/2 [89]	12	1-1/8 [29]	7/8 [22]	12-3/8 [314]	10-5/8 [270]	10-7/8 [277]	3-1/2 [89]
16							16						
20	1-3/8 [35]	1-1/8 [29]	11-1/2 [292]	9-1/2 [241]	12-1/8 [308]	3-5/8 [92]	20	1-3/8 [35]	1-1/8 [29]	12-1/2 [318]	10-1/2 [267]	12-1/8 [308]	3-5/8 [92]
30	1-5/8 [42]		11-5/8 [295]	9-3/8 [238]	13-3/8 [340]		30	1-5/8 [42]		12-5/8 [321]	10-3/8 [264]	13-3/8 [340]	
40	2-1/8 [54]	1-3/8 [35]	11-3/4 [298]	9-1/4 [235]	14-5/8 [372]	3-3/4 [96]	40	2-1/8 [54]	1-3/8 [35]	12-3/4 [324]	10-1/4 [260]	14-5/8 [372]	3-3/4 [96]

NOTES:

- All dimensions are Inches [millimeters].
All dimensions are ±1/2" [13mm].
Metric values are soft conversion.
- All connections are ODM copper sweat unless otherwise noted.
- Field piping should be based on job requirements, not unit connection size.

TITLE:

BLOWER COIL UNIT
1 ROW STEAM HEATING
COIL CONNECTION LOCATION



DRN BY: WRG	DATE: 12/04/19	SCALE: 1=22	DRAWING NO.
CKD BY: TW	DATE: 12/04/19	REV: A	

THIS DRAWING CONTAINS PROPRIETARY DATA.
UNAUTHORIZED DISCLOSURE, REPRODUCTION, OR USE
IS STRICTLY PROHIBITED WITHOUT WRITTEN PERMISSION

DO NOT SCALE DRAWING
DIMENSIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE.
CONTACT FACTORY FOR CERTIFIED DRAWINGS.

CCC-031