


FIG. 1
1, 2, 4, AND 6 ROW (2-PIPE)



INTERNAL COIL												
UNIT SIZE	1 ROW			2 ROW			4 ROW			6 ROW		
	CONN. SIZE	A	B	CONN. SIZE	A	B	CONN. SIZE	A	B	CONN. SIZE	A	B
08	5/8 [16]	8-1/4 [210]	21-1/2 [546]	5/8 [16]	8-1/4 [210]	21-15/16 [557]	7/8 [23]	7-1/4 [184]	21-3/4 [552]	7/8 [23]	8-1/4 [210]	21-3/4 [552]
12			25-7/8 [657]			26-1/4 [667]			26-1/4 [667]			26 [660]
16			28 [711]			28-7/16 [718]			28-1/4 [716]			28-3/8 [721]
20			34-1/2 [711]			34-7/8 [886]			33-5/8 [854]			34-11/16 [881]
25			30-3/16 [767]			30-5/8 [778]			30-1/2 [775]			31 [787]
30	7/8 [23]	34-1/2 [711]	7-1/4 [184]	34-7/8 [886]	1-1/8 [29]	7-1/16 [179]	34-7/8 [886]	1-3/8 [35]	20-1/8 [511]	34-3/8 [873]		

NOTES:

- All dimensions are Inches [millimeters]. All dimensions are $\pm 1/2$ " [13mm]. Metric values are soft conversion.
- Standard galvanized drain pan has 1-1/8" ODM copper connection. Optional stainless steel drain pan has 1" galvanized Sch. 40 threaded steel connection.
- 4-pipe units with internal coils have cooling and heating connections on opposite sides of unit.
- All internal heating coils are in the re-heat position.
- Dimensions are based on unit cabinet only, and do not include filter rack or base rail.

TITLE:

MODEL VB/VR SERIES C
BELT DRIVE BLOWER COIL UNIT
2 PIPE INTERNAL WATER
COIL CONNECTION LOCATIONS



ENVIRO-TEC®

DRN BY: PCP	DATE: 07/15/00	SCALE: 1=23	DRAWING NO.
CND BY: DOUG B.	DATE: 7/31/15	REV: 03	

BRC-001

THIS DRAWING CONTAINS PROPRIETARY DATA. UNAUTHORIZED DISCLOSURE, REPRODUCTION, OR USE IS STRICTLY PROHIBITED WITHOUT WRITTEN PERMISSION

DO NOT SCALE DRAWING
DIMENSIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE.
CONTACT FACTORY FOR CERTIFIED DRAWINGS.