

SPECIALTY PRODUCTS

Stainless Steel Return T70SS, T80SS Series



T70SS

STAINLESS
STEEL

The T70SS and T80SS series return grilles & registers are constructed of stainless steel. They are an excellent choice for corrosive environments and critical room applications. They are available with blades at 45° deflection (T70DSS, T80DSS) or 0° deflection (T70SS, T80SS). The stationary blades are spaced on 3/4" centers and are anchored with nylon pivots to prevent rattling. Standard construction for the T70SS and T80SS series is surface mount.

FEATURES

- Standard construction is #304 stainless steel (also available in #316 stainless steel)
- 45° or 0° blade deflection
- Horizontal or vertical face blades
- Countersunk screw holes & stainless steel screws
- Standard finish is satin polish (SP)

ACCESSORIES

- Stainless steel opposed blade damper (SSOBD)
- Stainless steel plaster frame

Available Sizes		
Model	Minimum	Maximum
T70SS T80SS	4x4	48x48
1" increments of width and height. Multiple sections furnished for sizes greater than maximum		