



DIMENSIONS - In [mm]

UNIT SIZE	H		W	L		MB (HU)		MB (VU)	
	HU	VU		HU	VU	A	B	A	B
08	21 [533]	44 [1118]	30 [762]	40 [1016]	24 [610]	18 [457]	21 [533]	18 [457]	21 [533]
12	21 [533]	44 [1118]	36 [914]	40 [1016]	24 [610]	18 [457]	21 [533]	18 [457]	21 [533]
16	21 [533]	44 [1118]	44 [1118]	40 [1016]	24 [610]	18 [457]	21 [533]	18 [457]	21 [533]
20	22-1/2 [572]	50 [1270]	50 [1270]	40 [1016]	30 [762]	21 [533]	22-1/2 [572]	21 [533]	21 [533]
30	30 [762]	56 [1422]	59 [1499]	46 [1168]	30 [762]	21 [533]	30 [762]	21 [533]	30 [762]
40	30 [762]	59 [1499]	68 [1727]	46 [1168]	30 [762]	24 [610]	30 [762]	24 [610]	30 [762]

- NOTES:**
1. All dimensions are Inches, [millimeters].
All dimensions are $\pm 1/4"$ [6mm].
Metric values are soft conversion.
 2. See dwg. 35-80050 for rigging hole and base rail details.
 3. This drawing is for identification of unit configuration only. See individual unit and section drawings for submittal details.
 4. Flat filter rack will be located as required.

TITLE: MODEL HDD/VDD DIRECT DRIVE BLOWER COIL UNIT UNIT CONFIGURATION		ENVIRO-TEC	
DRN BY: VSC	DATE: 06/17/21	SCALE: N/A	DRAWING NO.
THIS DRAWING CONTAINS PROPRIETARY DATA. UNAUTHORIZED DISCLOSURE, REPRODUCTION, OR USE IS STRICTLY PROHIBITED WITHOUT WRITTEN PERMISSION		DO NOT SCALE DRAWING DIMENSIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE. CONTACT FACTORY FOR CERTIFIED DRAWINGS.	
CKD BY: BL		DATE: 06/17/21 REV: A	
			35-80047