

## **PERFORATED DIFFUSERS**

## Modular Face PM, APM Series



**PM** 

STEEL BACKPAN ALUMINUM FACE

The versatile PM series model perforated ceiling diffusers are recommended for heating, ventilating and cooling applications in both constant and variable volume systems. The removable hinged perforated face blends with any ceiling.

The key to the PM diffuser lies in its four individual louver modules, which are removable and can be easily rotated in various directions to provide a multitude of pattern arrangements. The diffusers can be easily set in the field because the modules are adjustable without the use of tools.

## **FEATURES**

STEEL

- A multitude of air patterns can be achieved with a single diffuser
- Four individual louver modules can be set in a 1-way, 2-way, 3-way or 4-way air pattern and are adjustable without the use of tools
- Louver modules can be removed for access to the mounting Margin and neck damper
- Perforated face has 3/16" holes on 1/4" staggered centers and no less than 51% free area
- · Available in square neck only
- Standard finish is white (WH)

## ACCESSORIES

- Steel plaster Margin (SMF)
- Aluminum plaster Margin (ASMF)
- Dampers must be ordered separately and field installed (SMOBD, AMOBD)

Note: Trim frame and dampers are ordered separately and shipped loose for field installation.

PM, APM Available Sizes				
Neck Size (in.)	Margin Styles			
	SF	LT	TG	NR
6x6	X	Х	Х	Х
8x8	Х	Х	Х	Х
10x10	Х	Х	Х	Х
12x12	Х	Х	Х	Х
14x14	Х	Х	Х	Х
16x16	Χ	Х	Х	Х
18x18	Χ	Х	Х	Х
20x20	Х			

"X" denotes availability for both PM & APM