

## STANDARD FEATURES

## OPTIONAL FEATURES

### Discharge Plenum:

- Casing features to match basic unit
- Double deflection discharge grille

### Discharge Section:

- Casing features to match basic unit

### Mixing Box Section:

- Casing features to match basic unit
- Heavy gauge galvanized steel formed blade dampers with interconnecting damper linkage
- Low leakage type construction with blade edge and jamb seals
- Parallel blade operation
- 1/2" diameter round drive rods both sides
- Gasketed removable access plate
- Standard rear & top inlet locations
- 1" inlet collars

### Base Rail Assembly:

- 12 gauge galvanized steel construction
- 5/8" rigging holes
- Factory assembled to unit

- Factory selected and furnished floor mount, rubber-in-shear or spring type vibration isolators


### Electrical:

- All units ETL listed in compliance with UL/ANSI Standard 1995
- Fan motor wired to standard control enclosure

- Motor wiring in conduit
- Single phase fan control package
- Three phase fan control package
- Door interlocking disconnect switch (non-fused or fused)
- Main fusing
- Frequency inverters

### NOTES:

1. See individual unit and section drawings for dimensional details.
2. Unless otherwise noted, all sections are shipped factory mounted.
3. Optional mixing box section requires a base rail assembly.
4. See drawing CEH-001 for Electric Heat Sections.

REV. NO: 02	DATE: 7/02/03	BY: DI	REVISION DESCRIPTION: UPDATED TO MATCH CATALOG	
TITLE: MODEL VB/VR SERIES C BELT DRIVE BLOWER COIL UNIT ADDITIONAL SECTION FEATURES & OPTIONS				
<small>THIS DRAWING CONTAINS PROPRIETARY DATA. UNAUTHORIZED DISCLOSURE, REPRODUCTION, OR USE IS STRICTLY PROHIBITED WITHOUT WRITTEN PERMISSION.</small>				<small>DO NOT SCALE DRAWING. DIMENSIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE. CONTACT FACTORY FOR CERTIFIED DRAWINGS.</small>
DRN BY: HANK		DATE: 07/15/00	SCALE: NTS	DRAWING NO.
CKD BY: Hank		DATE: 7/7/03	REV: 02	VBR-002