

HOW TO SPECIFY


DDV

| MODEL | SENSOR | UNIT CONFIGURATION | | LINER | CASING OPTIONS | |
|-------|--|--|---|-------|------------------------|--|
| | | CONST. | SIDE | | | |
| DDV | | | | | | |
| | 3S - Inlet Sensing 3T - Total Air Sensing (Cold) 3H - Total Sensing (Hot) 3Y - Total Sensing (Cold & Hot) | | | | | |
| | | 0 - Standard Construction (no mixing baffle) 1 - Standard Construction (with mixing baffle) | | | | |
| | | | 0 - 1/2" Dual Density Lining 1 - 1" Dual Density Lining 2 - Insul-Guard™ (Rigid Duct Board) 3 - No liner 5 - Enviroseal™ (fiber free) | | | |
| | | | | | 0 - 22 Gauge 2 - 20 | |
| | | | | | | R - Right } Controls & Damper Side L - Left } |



HOW TO SPECIFY

DDV



| DDV Available Inlet Size Combinations | | | | | | | | | |
|---------------------------------------|---|---|---|---|---|----|----|----|----|
| Inlet Sizes | 4 | 5 | 6 | 7 | 8 | 10 | 12 | 14 | 16 |
| 4 | Y | Y | Y | - | - | - | - | - | - |
| 5 | Y | Y | Y | Y | - | - | - | - | - |
| 6 | Y | Y | Y | Y | Y | - | - | - | - |
| 7 | - | Y | Y | Y | Y | - | - | - | - |
| 8 | - | - | Y | Y | Y | Y | - | - | - |
| 10 | - | - | - | - | Y | Y | Y | - | - |
| 12 | - | - | - | - | - | Y | Y | Y | - |
| 14 | - | - | - | - | - | - | Y | Y | Y |
| 16 | - | - | - | - | - | - | - | Y | Y |

“Y” - Combination is available
 “-” - Combination not available

