




PRODUCT DIMENSIONS


T1100, A1100

Margin Details: SF, LT, PL, YM & NR


SF - Surface Mount




LT - Lay-in T-Bar




PL - Spline



YM - Snap-in



NR - Narrow Regress




Model	Module (in.)	Neck (in.)	A (in.)	B (in.)	C (in.)	Available Margin				
						SF	LT	PL	YM	NR
T1100	12x12	6	1-1/8	1-1/8	9	X	X	X	X	
		8	1-1/8	1-1/4	9	X	X	X	X	
	24x24	6,8	2-1/2	1-1/4	18	X	X	X	X	X
		10,12,14,15	2-1/2	1-3/8	18	X	X	X	X	X
A1100	12x12	6	1-1/8	1-1/8	9	X	X			
		8	1-1/8	1-1/4	9	X	X			
	24x24	6,8	2-1/2	1-1/4	18	X	X			X
		10,12,14,15	2-1/2	1-3/8	18	X	X			X
						"X" denotes				



PRODUCT DIMENSIONS

T1100, A1100 Insulation Blanket



Module (in.)	Available Margin Styles				
	SF	LT	PL	YM	NR
12x12					
24x24	X	X	X	X	
"X" denotes availability					