



NOTES:

1. All dimensions in Inches [millimeters]. All dimensions $\pm 1/4"$ [6mm].
2. Left Hand unit shown, Right Hand unit opposite.
3. Standard control enclosure is integrated into unit side. Includes (4) knockouts on (2) sides. Provide sufficient clearance to access electrical controls and comply with applicable codes and ordinances. NEC clearance is from the bottom of the unit.

INLET VALVE			
DIA.	"A"	"B"	\varnothing "I"
6"	18-1/8" [462]	22-1/2" [359]	5-7/8" [149]
8"	19-1/8" [486]	21-1/2" [333]	7-7/8" [200]
10"	20-1/8" [486]	20-1/2" [308]	9-7/8" [251]
COIL			
DIA.	"C"	"D"	-----
3/8"	16" [406]	1-1/8" [28]	-----
1/2"	15" [481]	2-1/8" [54]	-----
INDUCED AIR INLET			
----	"E"	"F"	----
----	16" [406]	16" [406]	----



THIS DRAWING CONTAINS PROPRIETARY DATA. UNAUTHORIZED DISCLOSURE, REPRODUCTION, OR USE IS STRICTLY PROHIBITED WITHOUT WRITTEN PERMISSION.

SUBMITTAL DRAWING
ALL DRAWINGS ARE SUBJECT TO CHANGE WITHOUT PRIOR NOTICE

DO NOT SCALE DRAWING
DIMENSIONS ARE IN INCH (MM) FORMAT +/- 1/8 (3) UNLESS OTHERWISE NOTED

TITLE:

MODEL CRB12 W/ HOT WATER COIL

DATE
07/30/20

SHEET
PAGE 1 OF 1

DRAWING NO
10-80012

REV
A