



DIMENSIONS - In [mm]

UNIT SIZE	A	B	SINGLE/DOUBLE SUPPLY		E	F
			C	D		
03 & 04	18 [457]	16-1/2 [419]	16 [406]	8 [203]	6 [152]	6.81 [173]
06 & 08	20 [508]	18-1/2 [470]	18 [457]	12 [305]	6 [152]	6.47 [164]
10 & 12	24 [610]	22-1/2 [572]	22 [559]	14 [356]	8 [203]	4.9 [124]

NOTES:

- All dimensions are Inches [mm]. Metric values are soft conversion.
- All dimensions are ±1/4 [6mm].
- Tile ring is installed on front of unit as shown, and may be moved to left or right side of unit in field. Tile ring omitted on units with "ADA" control mounting location.
- Wiring from electrical entry point to control enclosure is furnished and installed by others in field.
- Risers available from 3/4" [19mm] to 3" [76mm] diameter with 1/2" [13mm] thick insulation, and 3/4" [19mm] to 2-1/2" [64mm] diameter with 3/4" [19mm] thick insulation.
- Riser length is 120" [3048mm] max, 100" [2540mm] min.
- Back riser location shown. See arrangement drawings for available unit configurations.
- Factory mounted risers shown. See drawing VH-105 for shipped loose riser details.

TITLE: MODEL VHC, SIZE: 03-12 VERTICAL CONCEALED HIGH RISE FCU, 88" CABINET WITH RISERS			
THIS DRAWING CONTAINS PROPRIETARY DATA. UNAUTHORIZED DISCLOSURE, REPRODUCTION, OR USE IS STRICTLY PROHIBITED WITHOUT WRITTEN PERMISSION		DO NOT SCALE DRAWING DIMENSIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE. CONTACT FACTORY FOR CERTIFIED DRAWINGS.	
DRN BY: JCR	DATE: 11/17/10	SCALE: NA	DRAWING NO. 74-80050
CKD BY: DPB	DATE: 11/17/10	REV: 03	