



- Heavy extruded aluminum blades in a 20 gauge steel margin
- Individually adjustable, aerodynamically shaped blades on 3/4" spaced centers
- Available with both horizontal front blades and vertical front blades
- Available in sizes ranging from 6" x 4" to 48" x 48" in 1" increments; larger sizes will ship in multiple sections with assembly hardware for field assembly
- Standard finish is white (WH)

AVS54 - Horizontal Front Blades

AVS64 - Vertical Front Blades



Mounting Style

- A - External Screw Holes
- C - Concealed Screw Holes with Brackets
- N - No Screw Holes

Finish

- WH - White
- AP - Aluminum Paint
- OW - Off-White
- FB - Flat Black
- MP - Match Paint

Accessories

- SOBDS - Steel Opposed Blade Damper, Slot Operated
- AOBDS - Aluminum Opposed Blade Damper, Slot Operated
- ST - Earthquake Tabs
- SM - Insect Screen, 1/16" Square Mesh
- LM - Debris Screen, 1/4" Square Mesh
- 45 - Steel Plaster Frame
- A45 - Aluminum Plaster Frame

Dimensions in inches

Job: _____	Tag: _____	AVS54 / AVS64 AeroFoil Grille/Register Steel Margin Double Deflection 3/4" Blade Spacing
Location: _____	Submitted By: _____	
Architect: _____	SD - 2279 Rev: A (04/18)	
Engineer: _____		
Contractor: _____		