



DIMENSIONS - In [mm]

UNIT SIZE	A	B	SINGLE SUPPLY		E
			C	D	
03 & 04	18 [457]	16-1/2 [419]	16 [406]	8 [203]	6 [152]
06 & 08	20 [508]	18-1/2 [470]	18 [457]	12 [305]	6 [152]
10 & 12	24 [610]	22-1/2 [572]	22 [559]	14 [356]	8 [203]

- NOTES:
- All dimensions are Inches [mm]. Metric values are soft conversion.
 - All dimensions are $\pm 1/4$ [6mm].
 - Tile ring is installed on front of unit as shown, and may be moved to left or right side of unit in field. Tile ring omitted on units with "ADA" control mounting location.
 - Wiring from electrical entry point to control enclosure is furnished and installed in the field by others.
 - All piping and insulation between slave unit and risers is furnished and installed in the field by others.
 - Back connection location shown. See arrangement drawings for available unit configurations.
 - All coil and drain connections are "retracted" and braced internally for shipment.
 - Coil connections are 5/8" [16mm] O.D. female sweat. Drain "P-trap" is designed to accept 7/8" [22mm] O.D. copper tube.
 - Slave units are furnished with factory installed shutoff valves and field connection tubes, unless master unit risers are shipped loose. Risers may be shipped separately.

TITLE: MODEL VHS VERTICAL CONCEALED SLAVE HIGH RISE FCU, 88" CABINET			
DRN BY: DVG	DATE: 5/10/08	SCALE: n/a	DRAWING NO.
CKD BY:	DATE:	REV: 00	74-80008
<small>THIS DRAWING CONTAINS PROPRIETARY DATA. UNAUTHORIZED DISCLOSURE, REPRODUCTION, OR USE IS STRICTLY PROHIBITED WITHOUT WRITTEN PERMISSION.</small>			
<small>DO NOT SCALE DRAWING. DIMENSIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE. CONTACT FACTORY FOR CERTIFIED DRAWINGS.</small>			