### Table 3: Details Menu

Menu Option	Description	Range
Supply Air Tem- perature Setpoint	Controls to this value if the Supply Air Temp Reset Strategy is set to True.	Adjustable: 40 to 70°F (4 to 21°C)
Maximum Supply Temp Setpoint Adjust	Shows the maximum adjustment of the Supply Air Setpoint plus or minus set value, when set to True.	Adjustable: 30 to 480 minutes
Duct Pressure Setpoint	Controls to this value if the Duct Static Setpoint reset strategy is set to True.	Adjustable: 0.5 to 4.5 in. w.c.
Max Duct Static SP Adjust	Shows the max- imum adjust- ment of the duct pressure setpoint plus or minus set value, when set to True.	Adjustable: 0 to 0.5 in. w.c.
Economizer Minimum Position Setpoint	Sets the economizer's minimum position.	Adjustable: 0 to 100%

### **Additional Information**

Refer to the *Verasys System Operation Overview Technical Bulletin (LIT-12012370)* for more information on the various sequences performed by adjusting the control parameters.

For additional information about Verasys, use the QR code or visit www.verasyscontrols.com.



# European Single Point of Contact:

JOHNSON CONTROLS WESTENDHOF 3 45143 ESSEN GERMANY

### NA/SA Single Point of Contact:

JOHNSON CONTROLS 507 E MICHIGAN ST MILWAUKEE WI 53202 USA

#### **APAC Single Point of Contact:**

JOHNSON CONTROLS C/O CONTROLS PRODUCT MANAGEMENT NO. 22 BLOCK D NEW DISTRICT WUXI JIANGSU PROVINCE 214142 CHINA



(barcode for factory use only)





# **VERASYS**<sup>™</sup>

# Zone Coordinator - VAV

**QUICK START GUIDE** 









## **GETTING STARTED**

This guide provides the minimum configuration requirements you need to quickly bring the system communication and controls online with the Smart Building Hub (SBH).







Table 1: Unit Menu

Menu Option	Description	Range
Unit Enable	Validates that the unit is set to Enable.	Adjustable: Shutdown, Enable
Temporary Occupancy Timeout	Displays lockout value. The default value is 120 minutes. You can adjust the temporary occupancy for all zones from this location.	Adjustable: 30 to 480 minutes



# **Commissioning Menu**



**Table 2: Commissioning Menu** 

Menu Option	Description	Range
Control Mode	Validates that the unit is set to Auto.	Adjustable: Heat, Cool, Fan Only, Auto, Off
Balancer Mode	Enables Bal- ancer Mode. When you are not using the Balancer Mode, ensure this parameter is set to Off.	Adjustable: On, Off



# **Details Menu**

