


- Extruded aluminum construction
- Available slot widths are 1/2", 3/4", 1", 1 1/2", and 2"
- Available for 1 thru 8 slots for slot widths 1/2"-1", 1 thru 4 slots for 1 1/2"-2"
- Maximum single piece length is 72" (longer units will ship as multiple sections)
- Standard finish is painted white margins with black pattern controllers



SUPPLY



RETURN*







| 050 (1/2" slot width) | | | |
|-----------------------|--------|--------|---------|
| # Slots | W | A | B |
| 1 | 2 3/4 | 1 5/8 | 1 7/16 |
| 2 | 4 | 2 7/8 | 2 11/16 |
| 3 | 5 1/4 | 4 1/8 | 3 15/16 |
| 4 | 6 1/2 | 5 3/8 | 5 3/16 |
| 5 | 7 3/4 | 6 5/8 | 6 7/16 |
| 6 | 9 | 7 7/8 | 7 11/16 |
| 7 | 10 1/4 | 9 1/8 | 8 15/16 |
| 8 | 11 1/2 | 10 3/8 | 10 3/16 |

| 075 (3/4" slot width) | | | |
|-----------------------|--------|--------|----------|
| # Slots | W | A | B |
| 1 | 3 | 1 7/8 | 1 11/16 |
| 2 | 4 1/2 | 3 3/8 | 3 3/16 |
| 3 | 6 | 4 7/8 | 4 11/16 |
| 4 | 7 1/2 | 6 3/8 | 6 3/16 |
| 5 | 9 | 7 7/8 | 7 11/16 |
| 6 | 10 1/2 | 9 3/8 | 9 3/16 |
| 7 | 12 | 10 7/8 | 10 11/16 |
| 8 | 13 1/2 | 12 3/8 | 12 3/16 |

| 100 (1" slot width) | | | |
|---------------------|--------|--------|----------|
| # Slots | W | A | B |
| 1 | 3 1/4 | 2 1/8 | 1 15/16 |
| 2 | 5 | 3 7/8 | 3 11/16 |
| 3 | 6 3/4 | 5 5/8 | 5 7/16 |
| 4 | 8 1/2 | 7 3/8 | 7 3/16 |
| 5 | 10 1/4 | 9 1/8 | 8 15/16 |
| 6 | 12 | 10 7/8 | 10 11/16 |
| 7 | 13 3/4 | 12 5/8 | 12 7/16 |
| 8 | 15 1/2 | 14 3/8 | 14 3/16 |

| 150 (1 1/2" slot width) | | | |
|-------------------------|--------|-------|---------|
| # Slots | W | A | B |
| 1 | 3 3/4 | 2 5/8 | 2 7/16 |
| 2 | 6 | 4 7/8 | 4 11/16 |
| 3 | 8 1/4 | 7 1/8 | 6 15/16 |
| 4 | 10 1/2 | 9 3/8 | 9 3/16 |

| 200 (2" slot width) | | | |
|---------------------|--------|--------|---------|
| # Slots | W | A | B |
| 1 | 4 1/4 | 3 1/8 | 2 15/16 |
| 2 | 7 | 5 7/8 | 5 11/16 |
| 3 | 9 3/4 | 8 5/8 | 8 7/16 |
| 4 | 12 1/2 | 11 3/8 | 11 3/16 |



| Slot Width | |
|------------|-----|
| 050 | 075 |
| 100 | 150 |
| 200 | |

- Finish**
- White
 - Mill
 - Clear Anodized
 - Aluminum Paint
 - Off White
 - Flat Black
 - Match Paint

*NOTE: Return option not available for 1 1/2" and 2" slot widths

Dimensions in inches

| | | |
|-------------------|---------------------|--|
| Job: _____ | Tag: _____ | 6000 Slot Diffuser "B" Margin |
| Location: _____ | Submitted By: _____ | |
| Architect: _____ | | |
| Engineer: _____ | | |
| Contractor: _____ | SD - 2111 | Rev: D (11/12) |