

3 ROW WATER COIL

With 2 Row HW Pre-heat Coil

DIMENSIONS - In [mm]

See Dwg.
CCC-001, Fig. 3

STANDARD CIRCULATION					
UNIT SIZE	COIL CONNEX	A	B	C	D
08	7/8 [23]	10 [254]	7-3/4 [197]	4-1/8 [105]	15-3/4 [401]
12					
16					
20	1-1/8 [29]	10 [254]	7-3/4 [197]	4-1/8 [105]	18-3/8 [467]
30					20-7/8 [531]
40					23-3/8 [594]

'LO GPM' CIRCULATION						'HIGH GPM' CIRCULATION					
UNIT SIZE	COIL CONNEX	A	B	C	D	UNIT SIZE	COIL CONNEX	A	B	C	D
08	5/8 [16]	10 [254]	7-3/4 [197]	4-1/8 [105]	15-3/4 [401]	08	7/8 [23]	10 [254]	7-3/4 [197]	4-1/8 [105]	15-3/4 [401]
12						12					
16	7/8 [23]	10 [254]	7-3/4 [197]	4-1/8 [105]	18-3/8 [467]	16	1-1/8 [29]	10 [254]	7-3/4 [197]	4-1/8 [105]	18-3/8 [467]
20						20					
30	1-1/8 [29]	10 [254]	7-3/4 [197]	4-1/8 [105]	20-7/8 [531]	30	1-3/8 [35]	10 [254]	7-3/4 [197]	4-1/8 [105]	20-5/8 [524]
40					23-3/8 [594]	40					4-3/8 [112]

NOTES:

1. All dimensions are Inches [millimeters].
All dimensions are ±1/2" [13mm].
Metric values are soft conversion.
2. All connections are ODM copper sweat unless otherwise noted.
3. Field piping should be based on job requirements, not unit connection size.

TITLE:

BLOWER COIL UNIT
3 ROW WATER COIL W/2 ROW HW PRE-HEAT
COIL CONNECTION LOCATION



DRN BY: WRG	DATE: 12/04/19	SCALE: 1=22	DRAWING NO.
CKD BY: TW	DATE: 12/04/19	REV: A	

CCC-041

THIS DRAWING CONTAINS PROPRIETARY DATA.
UNAUTHORIZED DISCLOSURE, REPRODUCTION, OR USE
IS STRICTLY PROHIBITED WITHOUT WRITTEN PERMISSION

DO NOT SCALE DRAWING
DIMENSIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE.
CONTACT FACTORY FOR CERTIFIED DRAWINGS.