


DIMENSIONS - In [mm]

VHA (MASTER)	VHB (SLAVE)	A	B	C	D	VHA SUPPLY AIR				VHB SUPPLY AIR			
						SINGLE	DOUBLE	TOP		SINGLE	DOUBLE	TOP	
						E	E	F	G	E	E	F	G
03 or 04	03 or 04	18 [457]	42-1/4 [1073]	16-1/2 [419]	16 [406]	8 [203]	8 [203]	6 [152]	8 [203]	8 [203]	8 [203]	6 [152]	8 [203]
03 or 04	06 or 08	20 [508]	46-1/4 [1175]	18-1/2 [470]	18 [457]	8 [203]	8 [203]	6 [152]	12 [305]	8 [203]	8 [203]	6 [152]	12 [305]
03 or 04	10 or 12	24 [610]	54-1/4 [1378]	22-1/2 [572]	22 [559]	8 [203]	8 [203]	8 [203]	12 [305]	-- --	8 [203]	8 [203]	12 [305]
06 or 08	03 or 04	20 [508]	46-1/4 [1175]	18-1/2 [470]	18 [457]	8 [203]	8 [203]	6 [152]	12 [305]	8 [203]	8 [203]	6 [152]	12 [305]
06 or 08	06 or 08												
06 or 08	10 or 12	24 [610]	54-1/4 [1378]	22-1/2 [572]	22 [559]	8 [203]	8 [203]	8 [203]	12 [305]	-- --	8 [203]	8 [203]	12 [305]
10 or 12	03 or 04	24 [610]	54-1/4 [1378]	22-1/2 [572]	22 [559]	-- --	8 [203]	8 [203]	14 [356]	-- --	8 [203]	8 [203]	14 [356]
10 or 12	06 or 08												
10 or 12	10 or 12												

See page 1 of 2 for notes:

TITLE: MODEL VHA/VHB ENVIRO-PAC™ FIRE RATED AND NON-FIRE RATED FCU COMBINATIONS 79" CABINETS		
	DRN BY: JCR CKD BY: JR	DATE: 5/10/02 DATE: 5/26/17
THIS DRAWING CONTAINS PROPRIETARY DATA. UNAUTHORIZED DISCLOSURE, REPRODUCTION, OR USE IS STRICTLY PROHIBITED WITHOUT WRITTEN PERMISSION	DO NOT SCALE DRAWING DIMENSIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE. CONTACT FACTORY FOR CERTIFIED DRAWINGS.	DRAWING NO. VH-006