



- NOTES:
1. MAXIMUM 25 VA.
 2. MAXIMUM 10 VA.
 3. EARTH GROUNDING OF CHASSIS MUST BE PROVIDED BY OTHERS IN THE FIELD. (IF REQUIRED).
 4. COMPONENT LOCATED IN HEATER CABINET REFER TO HEATER WIRING DIAGRAM.
 5. MAY BE DIRECT WIRE DEPENDING ON MOTOR TYPE.
 6. SUPPLIED, MOUNTED, WIRED AND/OR PIPED BY MFG.
 7. LOW TUBING IS BLUE, HIGH IS RED
 8. CONNECT CONTROLLER TO THERMOSTAT BETWEEN SA BUS. CONNECTION MAY ALSO BE MADE USING RJ45 JACK.
 9. MAY BE DIRECT WIRE DEPENDING ON MOTOR TYPE.
 10. SEE ORDER ACKNOWLEDGEMENT FOR OPTIONAL ITEM REQUIREMENTS.

LEGEND

	TUBING		FEMALE PIN		MALE PIN
	FACTORY WIRING		WIRE NUT		LEVER NUT
	MALE QUICK		AMP PLUG		GND RIVET
	FEMALE QUICK		6 TP		WALL NUT
	FIELD WIRING				
	OPTIONAL ITEM				

UNCONTROLLED DOCUMENT WHEN PRINTED

THIS DRAWING MAY NOT REFLECT THE MOST CURRENT REVISION. PLEASE CHECK TO MAKE SURE DRAWING IS CURRENT.

THIS DRAWING CONTAINS PROPRIETARY DATA. UNAUTHORIZED DISCLOSURE REPRODUCTION, OR USE IS STRICTLY PROHIBITED WITHOUT WRITTEN PERMISSION.

TITLE:	WD, FAN CONTROLS, FPC-ZEC204 SUBMITTAL	MATERIAL:	
--------	--	-----------	--

REVISION DESCRIPTION	ZONE	STANDARD APPLIED TOLERANCES
REVISED FOR ZEC DESIGN CHANGES (PRESSURE SW,SAT & DAT) AS PER SEQUENCE OF OPERATION		WELDING: LENGTH ±0.063 ANGULAR ±3° SQUARE ±0.063 Cu TUBING: CUT LENGTH ±0.063 FORMED LENGTH ±0.125 FORMED ANGLE ±5° SHEET METAL: HOLE DIA ±0.005 CUT SIZE ±0.031 CUT ANGLE ±1° CUT SQUARE ±0.016 FORMED DIM ±0.031 FORMED ANGLE ±3° FORMED SQUARE ±0.031
ECR NO. 3889	BY SP	DATE 03/29/19
	CK BY AR / JAC	DATE 03/29/19
DO NOT SCALE DRAWING DIMENSIONS ARE IN INCHES UNLESS OTHERWISE NOTED		SCALE PART NO. NTS 87-10989 -00
SHEET 87-10989		DRAWING NO 87-10989
REV 04		