



- Constructed of 22 Ga. galvanized steel
- 1/2" thick dual density fiberglass insulation meets requirements NFPA 90A and UL181
- Field adjustable fan speed control and automatic reset thermal cutout
- Backdraft damper
- Easy access to internal components for maintenance via removable bottom panel
- Flo-cross sensor averages readings across all four quadrants of inlet
- 24 volt control transformer and fan interlocking relay
- Induced air inlet attenuator
- Flanged discharge connection on electric reheat coil
- Positive pressure heater air flow switch
- Power and control terminal block
- 80/20 Ni-Cr element
- **ETL** listed; **AHRI** certified sound ratings



### Options:

- 20 Ga. galvanized steel construction
- PSC Motor (Standard)
  - 120 V 208V/240V 277V
- Optional Liners
  - 1" dual density fiberglass insulation
  - 1/2" Enviroseal
  - 1" Enviroseal
  - 1" Insulguard
- Dust tight control enclosure
- Hangar brackets
- Motor disconnect
- Motor fusing
- SSR proportional heat
- Door interlocking disconnect switch
  - Fused Non-Fused
- AC Solid State Relays
- Chicago Code
- Manual reset cutout
- Filter



\* Note: Digital or Analog control enclosure is 31" x 11 7/8",  
Pneumatic control enclosure is 17" x 15".

UNIT SIZE	INLET SIZE	HP	A	B	C	D	E	F	G	H	INDUCED		DISCHARGE		M
											I	J	K	L	
2	06	1/10	29	15	4 7/8	15	15	5 7/8	7 1/2	6 7/8	13	13	11 1/2	11 1/2	1 3/4
2	08	1/10	29	15	4 7/8	15	15	7 7/8	7 1/2	6 7/8	13	13	11 1/2	11 1/2	1 3/4
3	08	1/10	29	15	4 7/8	15	15	7 7/8	7 1/2	6 7/8	13	13	11 1/2	11 1/2	1 3/4
3	10	1/10	29	15	4 7/8	15	15	9 7/8	7 1/2	6 7/8	13	13	11 1/2	11 1/2	1 3/4
4	10	1/4	29	15	4 7/8	15	15	9 7/8	7 1/2	6 7/8	13	13	11 1/2	11 1/2	1 3/4
4	12	1/4	29	15	6 7/8	15	15	11 7/8	7 1/2	6 7/8	13	13	11 1/2	11 1/2	1 3/4
5	12	1/2	37	17 3/4	6 7/8	19	17 3/4	11 7/8	8 7/8	9	17	15 3/4	14	15 1/2	1 7/8
5	14	1/2	37	17 3/4	6 7/8	19	17 3/4	13 7/8	8 7/8	9	17	15 3/4	14	15 1/2	1 7/8
6	14	1/2	37	17 3/4	6 7/8	19	17 3/4	13 7/8	8 7/8	9	17	15 3/4	14	15 1/2	1 7/8
6	16	1/2	37	17 3/4	6 7/8	19	17 3/4	15 7/8	8 7/8	9	17	15 3/4	14	15 1/2	1 7/8
7	16	3/4	37	17 3/4	6 7/8	19	17 3/4	15 7/8	8 7/8	9	17	15 3/4	14	15 1/2	1 7/8

### Dimensions in inches

Job: _____	Tag: _____	<b>FPP</b> <b>Fan-Powered Terminal Unit</b> <b>Parallel or Variable</b> <b>Electric Reheat</b>
Location: _____	Submitted By: _____	
Architect: _____		
Engineer: _____		
Contractor: _____	SD - 2191      Rev: B (03/17)	