



DISCHARGE END VIEW

INLET VALVE			
DIA.	"A"	"B"	Ø "I"
6"	18-1/8" [462]	14-1/8" [359]	5-7/8" [149]
8"	19-1/8" [486]	13-1/8" [333]	7-7/8" [200]
10"	20-1/8" [486]	12-1/8" [308]	9-7/8" [251]
COIL			
DIA.	"C"	"D"	-----
3/8"	12" [305]	2-1/8" [54]	-----
1/2"	12-1/2" [317]	1-5/8" [41]	-----
INDUCED AIR INLET			
--	"E"	"F"	--
--	12" [305]	13" [330]	--

NOTES:

1. All dimensions in Inches [millimeters]. All dimensions $\pm 1/4"$ [6mm].
2. Left Hand unit shown, Right Hand unit opposite.
3. Standard control enclosure is integrated into unit side. Includes (4) knockouts on (2) sides. Provide sufficient clearance to access electrical controls and comply with applicable codes and ordinances. NEC clearance is from the bottom of the unit.



THIS DRAWING CONTAINS PROPRIETARY DATA. UNAUTHORIZED DISCLOSURE, REPRODUCTION, OR USE IS STRICTLY PROHIBITED WITHOUT WRITTEN PERMISSION.

SUBMITTAL DRAWING
ALL DRAWINGS ARE SUBJECT TO CHANGE WITHOUT PRIOR NOTICE

DO NOT SCALE DRAWING
DIMENSIONS ARE IN INCH (MM) FORMAT
1/8" (3) UNLESS OTHERWISE NOTED

TITLE:

MODEL CRB10 W/ HOT WATER COIL

DATE

10/13/20

SHEET

PAGE 1 OF 1

DRAWING NO

10-80011

REV

A