




- Constructed of 22 Ga. galvanized steel
- 1/2" thick dual density fiberglass insulation meets requirements NFPA 90A and UL181
- Field adjustable fan speed control
- Easy access to internal components for maintenance via removable bottom panel
- Flo-cross sensor averages readings across all four quadrants of inlet
- 24 volt control transformer for electronic controls
- Induced air inlet attenuator
- **ETL listed; AHRI certified**



* NOTE: Digital or Analog enclosure is 20" x 11 7/8"
Pneumatic enclosure is 17" x 15"

Options:

- 20 Ga. galvanized steel construction
- PSC Motor (Standard)
 - 120 V 208V/240V 277V
- EON Motor (Available on Unit Size 3 and 6)
 - Manual Controls Remote Controls
 - 120V 208V/240V 277V
- Liners
 - 1/2" dual density fiberglass insulation
 - 1" dual density fiberglass insulation
 - 1/2" Enviroseal
 - 1" Enviroseal
 - 1" Insulguard
- Dust tight control enclosure
- Hangar brackets
- Motor disconnect
- Motor fusing
- Filter



UNIT SIZE	INLET SIZE	PSC HP	EON HP	A	B	C	D	E	F	G	H	I
2	6	1/10	-	21	12	11	4 7/8	5 7/8	7 1/2	5 3/8	15	6 3/4
3	6	1/4	1/2	21	12	11	4 7/8	5 7/8	7 1/2	5 3/8	15	9 1/4
3	8	1/4	1/2	21	12	11	4 7/8	7 7/8	7 1/2	5 3/8	15	9 1/4
4	8	1/4	-	32 1/4	17	16 1/2	4 7/8	7 7/8	8 7/8	5 3/8	17 3/4	11 7/8
4	10	1/4	-	32 1/4	17	16 1/2	4 7/8	9 7/8	8 7/8	7 3/8	17 3/4	11 7/8
4	12	1/4	-	32 1/4	17	16 1/2	6 7/8	11 7/8	8 7/8	8 3/8	17 3/4	11 7/8
5	10	1/2	-	32 1/4	17	16 1/2	4 7/8	9 7/8	8 7/8	7 3/8	17 3/4	13 1/8
5	12	1/2	-	32 1/4	17	16 1/2	6 7/8	11 7/8	8 7/8	8 3/8	17 3/4	13 1/8
6	10	3/4	1	32 1/4	17	16 1/2	4 7/8	9 7/8	8 7/8	7 3/8	17 3/4	13 1/8
6	12	3/4	1	32 1/4	17	16 1/2	6 7/8	11 7/8	8 7/8	8 3/4	17 3/4	13 1/8
6	14	3/4	1	32 1/4	17	16 1/2	6 7/8	13 7/8	8 7/8	8 3/8	17 3/4	13 1/8

Dimensions in inches

Job: _____	Tag: _____	FPS Fan-Powered Terminal Unit Series or Constant
Location: _____	Submitted By: _____	
Architect: _____		
Engineer: _____		
Contractor: _____	SD - 2183	Rev: C (03/17)