


- Constructed from galvanized steel
- Standard nominal lengths are 24, 36, 48, and 60 inches
- Optional internal insulation (does not include endcaps)
- Optional internal baffling widens spread by shortening the throw



Dimensions in inches

Nominal Length, N	Standard Inlets
24, 36	6, 8
48, 60, 72	6, 8, 10, 12*

Slot Widths

1/2" 3/4" 1"
1 1/2" 2"

Margin Style	Profile	H
A, B, C, N, S, T	Low	7 5/8
	High	10 5/8
F, G	Low	8
	High	11

Standard Inlet Sizes	A	B
6	6 1/4	5 1/4
8	9 3/8	5 1/4
10	12 1/2	5 1/4
12*	14 1/8	7 7/8

Standard Lengths

24" 36" 48"
60" 72"

Margin Style

A B
C F
G N
S T

* NOTE: Standard inlet size 12 available on High Profile option only

Margin Style	End Fabrication	L
A, B, C, N, S, T	ECP, ECL/R	N - 7/8
	INT, FECP	N - 1/4
F, G	ECP, ECL/R	N - 1/4
	INT, FECP	N - 1/4

Options

Low Profile High Profile
Internal Baffling Insulation
Inlet Damper (Shipped Loose for field installation)

End Fabrication

ECP
ECL / ECR
INT
FECP

Margin Style	Slot Width	W							
		Number of Slots							
		1	2	3	4	5	6	7	8
A, B, N, S, T	1/2	1 7/16	2 11/16	3 15/16	5 3/16	6 7/16	7 11/16	8 15/16	10 3/16
	3/4	1 11/16	3 3/16	4 11/16	6 3/16	7 11/16	9 3/16	10 11/16	12 3/16
	1	1 15/16	3 11/16	5 7/16	7 3/16	8 15/16	10 11/16	12 7/16	14 3/16
	1 1/2	2 7/16	4 11/16	6 15/16	9 3/16	11 7/16	13 11/16	15 15/16	18 3/16
	2	2 15/16	5 11/16	8 7/16	11 3/16	13 15/16	16 11/16	19 7/16	22 3/16
C, F, G	1/2	2 3/16	3 7/16	4 11/16	5 15/16	7 3/16	8 7/16	9 11/16	10 15/16
	3/4	2 7/16	3 15/16	5 7/16	6 15/16	8 7/16	9 15/16	11 7/16	12 15/16
	1	2 11/16	4 7/16	6 3/16	7 15/16	9 11/16	11 7/16	13 3/16	14 15/16
	1 1/2	3 3/16	5 7/16	7 11/16	9 15/16	12 3/16	14 17/16	16 11/16	18 15/16
	2	3 11/16	6 7/16	9 3/16	11 15/16	14 11/16	17 7/16	20 3/16	22 15/16

Job: _____
Location: _____
Architect: _____
Engineer: _____
Contractor: _____

Tag: _____
Submitted By: _____
SD - 2120 Rev: E (08/13)

LP
6000 Plenum