



SPECIFICATIONS

T70SS, T70DSS, T80SS, T80DSS

T70SS, T70DSS, T80SS, T80DSS Suggested Specification:

The stainless steel return grille shall be Tuttle & Bailey model T70SS (horizontal blades) or T80SS (vertical blades). The grille shall provide fixed blades on 3/4" centers. Construction shall be of 304 stainless steel with a 1-1/4" wide border on all sides with mitered corners. Blade deflection angle shall be available in 0° (T70SS/T80SS) or 45° (T70DSS/T80DSS). The grille shall be available with countersunk screw holes for a clean, unobtrusive appearance.

The finish shall be the Tuttle & Bailey Satin Polish (SP).

Optional volume adjustment damper (model SSOBD) shall be operable from the face and constructed of heavy gauge 304 stainless steel

The manufacturer shall provide published performance data tested in accordance with ANSI/ASHRAE Standard 70-1991 at isothermal conditions.

Model	Width	Height	Material	Frame Style	Module	Fastening Method	Damper	Finish
T70SS T70DSS T80SS T80DSS	4" to 48"	4" to 48"	304 - #304 Stainless Steel 316 - #316 Stainless Steel	SF - Surface Mount LT - Lay-in-T-Bar	None 24x24 48x24	01 - Screw Holes (Countersunk) 02 - No Screw Holes	00 - None SSOBD - Stainless Steel OBD	SP - #3 Satin Polish (Standard) WH - White

Example: T70SS - 38x38 - 304 - SF - None - 01 - SSOBD - SP

Specialty
Products