

T50SS, T60SS Suggested Specification:

Stainless steel single deflection supply grille shall be Tuttle & Bailey model T50SS (horizontal blades) or T60SS (vertical blades). The grille shall have individually adjustable blades on 3/4" centers. Construction shall be of #304 stainless steel with a 1-1/4" wide border on all sides with mitered corners. The grille shall be available with countersunk screw holes for a clean, unobtrusive appearance.

Optional volume adjustment damper (Models SS0BD) shall be operable from face and constructed of heavy gauge stainless steel.

The manufacturer shall provide published performance data tested in accordance with ANSI/ASHRAE Standard 70-1991 at isothermal conditions.

T54SS, T64SS Suggested Specification:

Stainless steel double deflection supply grille shall be Tuttle & Bailey model T54SS (horizontal front blades) or T64SS (vertical front blades). The grille shall have individually adjustable blades on 3/4" centers. Construction shall be of #304 stainless steel with a 1-1/4" wide border on all sides with mitered corners. The grille shall be available with countersunk screw holes for a clean, unobtrusive appearance.

Optional volume adjustment damper (Models SS0BD) shall be operable from face and constructed of heavy gauge stainless steel.

The manufacturer shall provide published performance data tested in accordance with ANSI/ASHRAE Standard 70-1991 at isothermal conditions.