




- Fixed (non-adjustable) aluminum blades
- Available in 0° deflection (A80) or 35° deflection (A80D)
- Aluminum construction
- Standard grille finish is white (WH)
- Damper option is mill finish only
- Available sizes are 6x4 to 48x48 in 1" increments (larger sizes in sections)



Concealed Mounting



LT Frame Style



Module	* Max Neck
12x12	9x9
24x12	21x9
24x24	21x21
48x24	45x21

Available Fastening Methods

- 01 - Screw Holes
- 02 - No Screw Holes
- 03 - Concealed (not available with AOBD)

Available Colors

White (WH) Mill (ML) Aluminum Paint (AP)
 Off-White (OW) Flat Black (FB)
 Match Paint (MP)

Accessories

AOBD - Aluminum opposed blade damper
 A45 - Aluminum mounting frame

* - When using a module for Lay-In T-Bar ceiling, this is the maximum neck size for specified module

Dimensions in inches

Job: _____	Tag: _____	A80 & A80D Return Grille Aluminum Construction
Location: _____	Submitted By: _____	
Architect: _____		
Engineer: _____		
Contractor: _____	SD - 2065	Rev: A (10/09)