


- NOTES:**
- MINIMUM 25 VA  
NOTE: POWER CONSUMPTION REQUIREMENTS \* WILL VARY DEPENDING UPON FIELD SUPPLIED/MOUNTED ACCESSORIES.
  - MAXIMUM 10 VA.
  - SUPPLIED, MOUNTED, WIRED AND/OR PIPED BY MFG.
  - LOW TUBING IS BLUE, HIGH IS RED
  - EARTH GROUNDING OF CHASSIS MUST BE PROVIDED BY OTHERS IN THE FIELD. (IF REQUIRED).
  - REFER TO MOTOR WIRING DIAGRAM FOR TRANSFORMER AND FAN RELAY WIRING (IF APPLICABLE).
  - CONNECT CONTROLLER TO THERMOSTAT BETWEEN SA BUS. CONNECTION MAY ALSO BE MADE USING RJ45 JACK.
  - SEE ORDER ACKNOWLEDGEMENT FOR OPTIONAL ITEM REQUIREMENTS.



UNCONTROLLED DOCUMENT WHEN PRINTED

THIS DRAWING MAY NOT REFLECT THE MOST CURRENT REVISION. PLEASE CHECK TO MAKE SURE DRAWING IS CURRENT.

THIS DRAWING CONTAINS PROPRIETARY DATA. UNAUTHORIZED DISCLOSURE REPRODUCTION, OR USE IS STRICTLY PROHIBITED WITHOUT WRITTEN PERMISSION.

REVISION DESCRIPTION		ZONE		STANDARD APPLIED TOLERANCES	
REVISED FOR ZEC DESIGN CHANGES (PRESSURE SW,SAT & DAT) AS PER SEQUENCE OF OPERATION				WELDING: LENGTH ±0.063 ANGULAR ±3° SQUARE ±0.063 Cu TUBING: CUT LENGTH ±0.063 FORMED LENGTH ±0.125 FORMED ANGLE ±5° SHEET METAL: HOLE DIA ±0.005 CUT SIZE ±0.031 CUT ANGLE ±1° CUT SQUARE ±0.016 FORMED DIM ±0.031 FORMED ANGLE ±3° FORMED SQUARE ±0.031	
ECR NO.	BY	DATE	CK BY	DATE	DO NOT SCALE DRAWING DIMENSIONS ARE IN INCHES UNLESS OTHERWISE NOTED
3889	SP	03/28/19	AR / JAC	03/28/19	

TITLE:		MATERIAL:	
WD, FAN CONTROLS, FPC-ZEC201 SUBMITTAL			
SCALE	PART NO.	SHEET	DRAWING NO.
NTS	87-10986 -00		87-10986
		REV	
		03	