



- Constructed of 22 Ga. galvanized steel
- 1/2" thick dual density fiberglass insulation meets requirements NFPA 90A and UL181
- Field adjustable fan speed control
- Backdraft damper
- Easy access to internal components for maintenance via removable bottom panel
- Flo-cross sensor averages readings across all four quadrants of inlet
- 24 volt control transformer for electronic controls
- Induced air inlet attenuator
- Hot water coil with 5/8" O.D. connection, 1/2" O.D. copper tubes, 20 Ga. steel casing & 10 FPI
- Available with 1-row or 2-row water coil
- Flanged discharge connection on hot water coil
- **ETL** listed; **AHRI** certified sound ratings



Options:

- 20 Ga. galvanized steel construction
- PSC Motor (Standard)
 - 120 V 208V/240V 277V
- Optional Liners
 - 1" dual density fiberglass insulation
 - 1/2" Enviroseal
 - 1" Enviroseal
 - 1" Insulguard
- Left Hand hot water coil connection
- Right Hand hot water coil connection
- Dust tight control enclosure
- Hangar brackets
- Motor disconnect
- Motor fusing
- Door interlocking disconnect switch
 - Fused Non-Fused
- Coil access door upstream of coil
- Filter



* Note: Digital or Analog control enclosure is 31" x 11 7/8",
Pneumatic control enclosure 17" x 15".

UNIT SIZE	INLET SIZE	HP	A	B	C	D	E	F	G	H	INDUCED		DISCHARGE		M
											I	J	K	L	
2	06	1/10	29	15	4 7/8	15	15	5 7/8	7 1/2	6 7/8	13	13	12 1/2	15	1 3/4
2	08	1/10	29	15	4 7/8	15	15	7 7/8	7 1/2	6 7/8	13	13	12 1/2	15	1 3/4
3	08	1/10	29	15	4 7/8	15	15	7 7/8	7 1/2	6 7/8	13	13	12 1/2	15	1 3/4
3	10	1/10	29	15	4 7/8	15	15	9 7/8	7 1/2	6 7/8	13	13	12 1/2	15	1 3/4
4	10	1/4	29	15	4 7/8	15	15	9 7/8	7 1/2	6 7/8	13	13	12 1/2	22	1 3/4
4	12	1/4	29	15	6 7/8	15	15	11 7/8	7 1/2	6 7/8	13	13	12 1/2	22	1 3/4
5	12	1/2	37	17 3/4	6 7/8	19	17 3/4	11 7/8	8 7/8	9	17	15 3/4	15	22	1 7/8
5	14	1/2	37	17 3/4	6 7/8	19	17 3/4	13 7/8	8 7/8	9	17	15 3/4	15	22	1 7/8
6	14	1/2	37	17 3/4	6 7/8	19	17 3/4	13 7/8	8 7/8	9	17	15 3/4	15	24 1/2	1 7/8
6	16	1/2	37	17 3/4	6 7/8	19	17 3/4	15 7/8	8 7/8	9	17	15 3/4	15	24 1/2	1 7/8
7	16	3/4	37	17 3/4	6 7/8	19	17 3/4	15 7/8	8 7/8	9	17	15 3/4	15	24 1/2	1 7/8

Dimensions in inches

Job: _____	Tag: _____	FPP Fan-Powered Terminal Unit Parallel or Variable Hot Water Heat
Location: _____	Submitted By: _____	
Architect: _____		
Engineer: _____		
Contractor: _____	SD - 2190 Rev: B (3/17)	