



SPECIFICATIONS

SDBS

SDBS Suggested Specification:

The security duct barrier shall be the Tuttle & Bailey SDBS security duct bars with sleeve. The duct barrier shall be constructed of 3/4" diameter round solid steel horizontal and vertical bars with a maximum of 6" centers. The bars shall be welded to the sleeve and the sleeve shall be stitch-welded along the seams. Two steel angle frames, 1-1/2"x 1-1/2" x 3/16", shall be shipped loose and unpainted for field mounting.

Finish shall be Tuttle & Bailey White (WH) electrocoat finish. The finish shall be an anodic acrylic paint, baked at 315°F for 30 minutes with a pencil hardness of HB to H.

Model	Width	Height	Sleeve Length	Finish
SDBS	6" to 30" in 2" increments	4" to 30" in 2" increments	06 - 6" 08 - 8" 10 - 10" 12 - 12" 18 - 18"	WH - White

Example: SDBS - 16 - 16 - 12 - WH