



T75DFB

GRILLES & REGISTERS

Tri-Flex Return-Filter Grilles T70FB, T80FB, T75FB, T85FB Series

STEEL

T70FB and T80FB filter return grilles have fixed bars spaced on 3/4" centers. Models T70DFB and T80DFB have face bars with 35° deflection. Models T70FB and T80FB have face bars with 0° deflection. The appearance matches the T50, T60 series supply grilles and registers.

T75FB and T85FB filter return grilles have fixed bars spaced on 1/2" centers. Models T75DFB and T85DFB have face bars with 35° deflection. Models T75FB and T85FB have face bars with 0° deflection. The appearance matches the T50, T60 series supply grilles and registers.

The streamlined bars and open spacing maintains an effective area capacity which minimizes intake velocity, reduces inlet pressure and provides quiet operation. Deflected bar grilles installed in a low or high sidewall location are vision proof with the bar deflection facing away from the line of sight.

FEATURES

- 1-1/4" nominal overlap margin
- Steel construction with welded borders and reinforced corners
- Available in 3/4" or 1/2" bar spacing
- 1" and 2" filter frames available
- Available in 35° or 0° deflection
- Knurled Knob or quarter turn fastener
- Standard finish is White (WH)

Available Sizes in One Piece

	Min	Max
SF Margin	8x8	48x36
LT Margin	8x8	44x20


Product available in one inch increments of width and height. Sizes greater than maximum width or height are not available.



T70DFB



T70FB



T85FB