



# SPECIFICATION

## RA50/RA54

### RA50/RA54 Suggested Specification:

Round supply grilles shall be Tuttle & Bailey models RA50 or RA54. The RA50 shall have one set of individually adjustable blades 3/4" on center for a clean appearance. The RA54 shall have two sets of individually adjustable blades 3/4" on center for a clean appearance. Construction of the blades shall be of heavy gauge extruded aluminum. The grille margin shall be constructed of aluminum and have a curved surface for a clean, unobtrusive appearance. The grille shall be mounted with an internal duct collar ring that will leave no visible fasteners from the room side of the grille.

The paint finish shall be Tuttle & Bailey White (WH) or mill (ML). The manufacturer shall provide published performance data tested in accordance with ANSI/ASHRAE Standard 70-1991 at isothermal conditions.

Model	Neck Size	Margin	Damper	Accessories	Finish
RA50 RA54	06 08 10 12 14 16 18 20	SF	0000 - None DMPR - Opposed Blade Damper*	DMR* - Duct Mounting Ring	WH - White AP - Aluminum Paint ML - Mill Finish FB - Flat Black

\*Duct mounting ring is required to mount damper. Damper is not available for sizes 18" and 20".