



INLET VALVE			
DIA.	"A"	"B"	Ø "I"
4"	18-1/8" [462]	14-1/8" [359]	3-7/8" [98]
5"	18-1/8" [462]	14-1/8" [359]	4-7/8" [124]
6"	18-1/8" [462]	14-1/8" [359]	5-7/8" [149]
8"	19-1/8" [486]	13-1/8" [333]	7-7/8" [200]
INDUCED AIR INLET			
----	"C"	"D"	----
----	12" [305]	13" [330]	----

**NOTES:**

1. All dimensions in Inches [millimeters]. All dimensions ± 1/4" [6mm].
2. Left Hand unit shown, Right Hand unit opposite.
3. Standard control enclosure is integrated into unit side. Includes (4) knockouts on (2) sides. Provide sufficient clearance to access electrical controls and comply with applicable codes and ordinances. NEC clearance is from the bottom of the unit.



THIS DRAWING CONTAINS PROPRIETARY DATA. UNAUTHORIZED DISCLOSURE, REPRODUCTION, OR USE IS STRICTLY PROHIBITED WITHOUT WRITTEN PERMISSION.

**SUBMITTAL DRAWING**  
ALL DRAWINGS ARE SUBJECT TO CHANGE WITHOUT PRIOR NOTICE

**DO NOT SCALE DRAWING**  
DIMENSIONS ARE IN INCH [MM] FORMAT +/- 1/8 [3] UNLESS OTHERWISE NOTED

TITLE:

**MODEL CRB07 COOLING ONLY**

DATE  
08/26/20

SHEET  
PAGE 1 OF 1

DRAWING NO  
10-80068

REV  
A