



INLET VALVE			
DIA.	"A"	"B"	$\phi$ "I"
10"	19-1/8" [486]	19-1/2" [495]	9-7/8" [251]
12"	20-1/8" [511]	18-1/2" [470]	11-7/8" [302]
14"	21-1/8" [562]	17-1/2" [445]	13-7/8" [352]
INDUCED AIR INLET			
----	"C"	"D"	----
----	14" [356]	18" [457]	----

**NOTES:**

1. All dimensions in Inches [millimeters]. All dimensions  $\pm 1/4"$  [6mm].
2. Left Hand unit shown, Right Hand unit opposite.
3. 90 degree control enclosure is perpendicular to the unit. Includes (4) knockouts on bottom. Provide sufficient clearance to access electrical controls and comply with applicable codes and ordinances.
4. NEC (36") clearance is straight out from control enclosure.



THIS DRAWING CONTAINS PROPRIETARY DATA. UNAUTHORIZED DISCLOSURE, REPRODUCTION, OR USE IS STRICTLY PROHIBITED WITHOUT WRITTEN PERMISSION.

**SUBMITTAL DRAWING**  
ALL DRAWINGS ARE SUBJECT TO CHANGE WITHOUT PRIOR NOTICE

**DO NOT SCALE DRAWING**  
DIMENSIONS ARE IN INCH [MM] FORMAT +/- 1/8 [3] UNLESS OTHERWISE NOTED

TITLE: <b>MODEL CRB25 COOLING ONLY 90 DEGREE ENCLOSURE</b>		DATE: 07/20/20	SHEET: PAGE 1 OF 1	DRAWING NO: 10-80092	REV: A
--	--	----------------	--------------------	----------------------	--------