



**DIMENSIONS - In [mm]**

UNIT SIZE	A	B	C	SINGLE/ DOUBLE SUPPLY		F
				D	E	
03 & 04	18 [457]	24 [610]	16-1/2 [419]	16 [406]	8 [203]	6 [152]
06 & 08	20 [508]	26 [660]	18-1/2 [470]	18 [457]	12 [305]	6 [152]
10 & 12	24 [610]	30 [762]	22-1/2 [572]	22 [559]	14 [356]	8 [203]

**NOTES:**

- All dimensions are Inches [mm]. Metric values are soft conversion.
- All dimensions are ±1/4 [6mm].
- Tile ring is installed on front of unit as shown, and may be moved to left or right side of unit in field. Tile ring is omitted on units with "ADA" control mounting location.
- Wiring from electrical entry point to control enclosure is furnished and installed by others in field.
- Risers available from 3/4" [19mm] to 3" [76mm] diameter with 1/2" [13mm] thick insulation, and 3/4" [19mm] to 2-1/2" [64mm] diameter with 3/4" [19mm] thick insulation.
- All piping and insulation between master and slave units is furnished and installed in the field by others.
- Riser length is 120" [3048mm] max, 100" [2540mm] min.
- Back riser location shown. See arrangement drawings for available unit configurations.
- Slave unit stubout dimension is approximate and varies with riser diameter. Stubout extends approximately 4" from riser tube.
- Water piping connections are 5/8" [16mm] O.D. and drain connection is 7/8" [22mm] O.D.
- Factory mounted risers shown. Risers may be shipped separately.

TITLE: MODEL VHM VERTICAL CONCEALED MASTER HIGH RISE FCU, 88" CABINET



DRN BY: ANTO	DATE: 5/09/08	SCALE: NA	DRAWING NO. 74-80007
CKD BY: DB	DATE: 6/12/08	REV: 00	

THIS DRAWING CONTAINS PROPRIETARY DATA. UNAUTHORIZED DISCLOSURE, REPRODUCTION, OR USE IS STRICTLY PROHIBITED WITHOUT WRITTEN PERMISSION

DO NOT SCALE DRAWING. DIMENSIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE. CONTACT FACTORY FOR CERTIFIED DRAWINGS.