

STANDARD FEATURES

Casing Construction:

- Galvanized 18 gauge steel casing
- 1" thick fiberglass insulation
- 1" supply duct collar
- Gasketed removable access panels sized for easy handling
- IAQ galvanized steel sloped drain pan with 1-1/8" ODM copper outlet one side.
- Right and left hand unit configuration

Fan Assembly:

- Forward curved fan
- Statically and dynamically balanced
- Solid steel shafting
- Ball bearings with design average life of 100,000 hours

Fan Motor and Drive:

- NEMA design ODP motors
- 1750 RPM single speed, 60 Hertz
- Single phase, 115, 208-230, and 277 volt
- Three phase, 208-230, 460, and 575 volt
- Slide type adjustable motor base
- Standard cross section "V-belt" drive with 1.2 design service factor
- Adjustable pitch motor pulley and fixed pitch blower pulley

Coils:

- 1/2" OD seamless copper tubes
- Collared and corrugated aluminum fins
- ARI 410 certified and labeled
- 300 PSIG working pressure @ 200°F
- Manual air vent fitting on all water coils
- Copper ODM sweat connections
- 0.016" tube wall on water coils and evaporator coils
- 0.025" tube wall on steam coils

Filters and Filter Rack:

- Side access flat filter rack
- Standard size 2" nominal thickness throwaway filters
- Hinged cover on external filter rack
- Standard filter rack designed to accept 2" thick filters

NOTES:

1. See individual unit and section drawings for dimensional details.

OPTIONAL FEATURES

- Scrim reinforced foil faced insulation
- Gasketed, hinged access panels with lift & turn latches
- Alternate fan discharge arrangements
- IAQ stainless steel sloped drain pan with 1" galvanized pipe outlet one side.
- Galvanized steel drain pan with 1-1/8" ODM copper outlet both sides
- Auxiliary (secondary) drain connections

- High efficiency three phase motors
- Spare set of drive belts

- 1, 2, 3, 4, and 6 row water coils
- 3, 4, and 6 row DX evaporator coils
- 1 and 2 row standard steam coils
- Heating coils in pre-heat or re-heat position
- Auto air vent on water coils
- Stainless steel coil casing
- 8, 10, 12, and 14 FPI fin spacing
- High and low GPM water coil circulation

- 2" pleated filters
- High efficiency filter rack to accept 2" and 4" thick filters
- Spare set of filters

TITLE:

MODEL H/V SERIES C
BELT DRIVE BLOWER COIL UNIT
FEATURES AND OPTIONS



DRN BY: JCR	DATE: 11/20/10	SCALE: 1=22	DRAWING NO.
CKD BY: DPB	DATE: 11/22/10	REV: 06	

CD-001

THIS DRAWING CONTAINS PROPRIETARY DATA.
UNAUTHORIZED DISCLOSURE, REPRODUCTION, OR USE
IS STRICTLY PROHIBITED WITHOUT WRITTEN PERMISSION

DO NOT SCALE DRAWING
DIMENSIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE.
CONTACT FACTORY FOR CERTIFIED DRAWINGS.